

drawer cabinet S – with fully extending drawers

ORION®

Application:

ideally suited to the storage of various tools and parts.

Execution:

- welded sheet-steel construction guarantees high loadability and stability
- central locking mechanism with safety lock and individual extension lock for drawers
- drawers capable of holding an evenly distributed load of up to 100 kg
- drawers with rows of slots for inserting dividers
- grid division (30:30 mm) facilitates custom compartmentalisation of drawers in housing
- plastic-coated worktop (black) with a thickness of 8 mm
- handle strips made from aluminium with labelling strips with transparent covers and cover caps



Art. no.	50100 070
Brand	ORION
Manufacturer Part Number	50100070
Number of drawers	5 PCS
Height	800 mm
Width	722 mm
Depth	700 mm
Height x width x depth	800 x 722 x 700 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	599 x 598 mm
Drawer with slots	Yes
Perforated drawer base	No
Load-carrying capacity per drawer	100 kg
Drawer surface	0.385 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	No
With single pull-out safety brake	Yes
Central locking	Yes
With cover panel	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Surface	Powder-coated
Functions	RFID possible
Overall surface	1.925 m ²
Lock type	Cylinder lock
Material	Sheet steel
Gross Weight	60.000 kg
Product Group	586

EAN

4053625401987