

Drawer cabinet system 700 S with 8 SOFT-CLOSE drawers

Depth 700 mm, width 722 mm

Application:

Particularly suitable for careful storage of delicate, sensitive tools and parts in drawers.

Advantage:

- The damping system brakes the drawer while closing; it closes the drawer smoothly and soundlessly by means of the self-closing mechanism
- Impact load on tools and parts stored in the drawer is reduced to a minimum due to the smooth-closing drawers
- High quality - made in Germany

FH mm	KH mm
60	40
60	40
90	70
90	70
90	70
90	70
120	100
120	100



Art. no.	50300 738
Brand	HK
Manufacturer Part Number	50300738
Number of drawers	8 PCS
Height	800 mm
Width	722 mm
Depth	700 mm
Height x width x depth	800 x 722 x 700 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 600 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	100 kg
Drawer surface	0.36 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	Yes
With single pull-out safety brake	Yes
Central locking	Yes
With cover panel	No
Material of cover panel	Wood, plastic-coated
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Functions	RFID possible
Model	S7 24/8
Overall surface	2.88 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	135.000 kg
Product Group	5BB

EAN

4053625049967