

# Surface Mount Schottky Barrier Rectifier



## Features:

- For surface mounted applications
- Metal-Semiconductor junction with guarding
- Epitaxial construction
- Very low forward voltage drop
- High current capability
- Plastic material has UL flammability classification 94V-0
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications.

## Mechanical Data:

Case	: Molded Plastic
Polarity	: Colour band denotes cathode
Weight	: 0.003 ounces, 0.093 grams
Reverse Voltage	: 20 to 100 Volts
Forward Current	: 2 Amperes

## Maximum Ratings and Electrical Characteristics:

Rating at 25°C ambient temperature unless otherwise specified.  
Single phase, half wave, 60Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

Type Number	Symbol	SS22	SS23	SS24	SS25	SS26	SS210	Unit
Max. Recurrent Peak Reverse Voltage	$V_{RRM}$	20	30	40	50	60	100	V
Max. RMS Voltage	$V_{RMS}$	14	21	28	35	42	70	
Max. DC Blocking Voltage	$V_{DC}$	20	30	40	50	60	100	
Max. Average Forward Rectified Current $T_L = 100^\circ\text{C}$	$I_{(AV)}$	2.0						A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	50						
Peak Forward Voltage at 2A DC	$V_F$	0.55			0.7		0.85	V
Max. DC Reverse Current at Rated DC Blocking Voltage at $T_J = 25^\circ\text{C}$ $T_J = 100^\circ\text{C}$	$I_R$	1 20						mA
Typical Junction Capacitance (Note 1)	$C_J$	200						pF
Typical Thermal Resistance (Note 2)	$R_{\theta JL}$	15						°C/W
Operating Temperature Range	$T_J$	-55 to + 150						°C
Storage Temperature Range	$T_{STG}$							






## Notes:

1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
2. Thermal resistance junction to lead.
3. The typical data above is for reference only

# Surface Mount Schottky Barrier Rectifier




## Ratings and Characteristic Curves



# Surface Mount Schottky Barrier Rectifier



## Dimensions:



Dimensions : Inches (Millimetres)

## Part Number Table

Description	Part Number
Surface Mount Schottky Barrier Rectifiers	SS22
	SS23
	SS24
	SS25
	SS26
	SS210

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com  
www.farnell.com  
www.newark.com

