

Threaded mounting bolt, can be rotated

Quick and easy-to-use attachment point

HALDER

Application:

For lifting loads. The threaded support bolt is inserted into a threaded hole and secures itself. In contrast to a ring screw, this eliminates time-consuming screwing and unscrewing.

Execution:

- Stop point with self-locking thread
- Shackles made of heat-treated steel, tempered, manganese phosphate-coated
- Stainless steel 1.4542 thread element, precipitation-hardened
- Movable shackle
- Loosen the safety bar to prevent accidental release
- High-strength, precipitation-hardened bolts
- Aluminium press stud
- TÜV tested - in accordance with DIN EN 13155

Advantage:

- Time savings of up to 95% compared to conventional ring bolts



Art. no.	77241 113
Brand	HALDER
Manufacturer Part Number	22353.0016
Thread dimension	M16
Load-carrying capacity	840 kg
Material of shackles	Steel tempered
Surface of the shackle	Manganese phosphated
Material of bolt	Steel tempered
Material of spring	Corrosion resistant steel
Material of push knob	Aluminium
Weight	597 g
Max. temperature	250 °C
Design	Self-locking
Operation	By pressing the button
With corrosion protection	Yes
Length to centre of bolt	17 mm
Bolt length	24 mm
Length 3	25.7 mm
Bolt length above	54.9 mm
Interior height	42.5 mm
Internal width	46 mm
External width	68 mm
Height	123.7 mm
Outer diameter	13.8 mm
Diameter bolt top	20 mm
Thread length	12 mm
Gross Weight	0.597 kg
Product Group	7EC

EAN

4030618716242