

All Purpose Adhesive

GENERAL PURPOSE SOLVENT-BORNE ADHESIVE

Date: 27 October 2015 Fact Sheet No.: TDS00410

YOUR SMART ADVANTAGES		
– Extra st	rong	
– Quick dr	rying	
	of materials	

USES

Bostik All Purpose Adhesive is a multipurpose solventborne adhesive, the dried film of which is virtually colourless and non-staining. It is quick drying, clean to use and provides strong, water-resistant bonds with excellent ageing properties.

Bostik All Purpose Adhesive will bond a wide variety of materials including metals, wood, glass, china, leather, felt, canvas, paper, cardboard, certain fabrics, PVC and various other plastics. It will bond all these materials to themselves or to each other as well as to plaster, stone and concrete.

Bostik All Purpose Adhesive is ideally suited for many assembly and repair applications in and around the home and other locations. Typical items on which it is used are handbags, luggage, lampshades, picture frames, upholstery, jewellery, books, china and marquetry pieces.

Bostik All Purpose Adhesive is excellent for bonding vinyl and plasticised PVC without the associated problems of migration that most other adhesives suffer.

PRODUCT CHARACTERISTICS		
Colour	Colourless	
Form	Mobile Liquid	
Specific Gravity	0.86 approx.	

Composition	Nitrile rubber/resin based solution in a mixture of ketone solvents		
Product Code	30813292 20ml Boxed 1 x 24 30813296 20ml Blister cards x 6 30803648 50ml Blister cards x 6		
Storage/Shelf Life	Store for up to 24 months from date of manufacture when stored in the original, unopened packaging under dry conditions within the temperature range of +5°C to +25°C. Store away from sources of ignition.		
TYPICAL PERFORMANCE DATA (Approx.)			
Setting Times	Bond within 10 minutes. Fully set in a few hours.		
Flammability	Highly flammable. Flashpoint: 18°C		

DIRECTIONS FOR USE

Service Temperature

Water Resistance

IMPORTANT: Before using Bostik All Purpose Adhesive refer to the relevant Health & Safety Data Sheet, available at www.bostik.co.uk.

-40°C to +80°C

Good

PREPARATION

- Make sure that the surfaces to be bonded are clean, dry and free from dust, dirt, grease and any other contaminants.
- 2. Protect nearby polished, cellulose or any other solvent sensitive surfaces as the adhesive may spoil the finish.



APPLICATION

- 3. To bond non-absorbent surfaces such as metal or glass apply a thin film of adhesive to both surfaces. Allow 5 to 10 minutes drying time and then, having correctly positioned the surfaces, press them together firmly. The bond will be instant and non-adjustable.
- 4. If one or both surfaces are absorbent apply a generous film of adhesive to one surface only and immediately join the two surfaces together under pressure. Immobilise the items until the solvent has evaporated. Using this technique initial bond strength may be a little lower.

CLEANING

- 5. Remove surplus adhesive by the use of nail polish remover or acetone.
- Dry adhesive is not easy to remove, particularly from sensitive surfaces where the solvent in the adhesive may have already caused damage. It is advisable to work carefully and protect such surfaces to reduce the problem.

PRECAUTIONS IN USE

Bostik All Purpose Adhesive will not bond polythene (polyethylene), polypropylene or Teflon. Bostik All Purpose Adhesive is unsuitable for use on polystyrene, cellulose paint, rayon, acetate fabrics and other man-made materials. This is because the solvent in the adhesive will damage the materials. Bostik All Purpose Adhesive is unsuitable for repairing pottery handles or other items that contain hot food and liquids.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit www.bostik.co.uk for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for Bostik All Purpose Adhesive, available at www.bostik.co.uk.





This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales Tel: 0844 371 1192 Fax: 01785 241818 customer.service@bostik.com
Technical Advice Tel: 0844 371 1197 Fax: 01785 272867 technical.service@bostik.com
Technical Data & COSHH (MSDS) Data Sheets Tel: 01785 272625 Fax: 01785 212962 stafford.gatehouse@bostik.com

