

SDJC clamp holder positive, left-hand

For longitudinal and copy turning with DC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with DC indexable insert 55°

Version

- Precision-made steel carrier, burnished, hardened, type D, attack angle 93°, tip angle 55°, clearance angle 7°

Advantage

- Narrow geometry optimised for contour-turning work
- Positive body geometry ensures low cutting forces
- Very good surfaces, for medium and finishing infeed



Art. no.	17831 027
ISO name	SDJC R/L 10 10 E07
Shaft height	10 mm
Shank width	10 mm
Length	70 mm
Length of head	13 mm
Programming size	12 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Left
DIN	4983

EAN-Code

4050293566369