

## SRGC clamping holder, positive, right

For copy, longitudinal face lathing with RC indexable insert

**ATORN**<sup>®</sup>

### Application

For longitudinal turning with RC indexable insert

### Version

- Precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, clearance angle 7°

### Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



<b>Art. no.</b>	<b>17850 517</b>
<b>ISO name</b>	SRGC R/L 2020 K10
<b>Shaft height</b>	20 mm
<b>Shank width</b>	20 mm
<b>Length</b>	125 mm
<b>Length of head</b>	17.2 mm
<b>Programming size</b>	25 mm
<b>Suitable for indexable inserts</b>	RC.. 1003..
<b>Tool design</b>	Left

### EAN-Code

4050293563146