

Lever gauge probe

TESATAST - lateral



Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts of boreholes and aligning workpieces.

Execution:

- Rotating dial
- Anti-magnetic components
- Automatic switching of callipers direction
- Measuring mechanism on ruby bearings
- Housing made from one piece, brushed chromium-plated
- Gauge slide with hard chrome-plated ball
- Lateral

Advantage:

- 3 dovetail mounting surfaces

Delivery:

TESATAST measuring probe with 2 mm ball diameter, clamping shaft diameter 8 mm, key disc, in plastic case



Art. no.	33346 050
Brand	TESA
Manufacturer Part Number	01810012
Length measuring range	2 mm
Scale value	0.02 mm
Measurement force	0.15 N
Length of measuring sensor from centre of ball	36.5 mm
Ball diameter	2 mm
Pivot range of measuring sensor	240 Degree
Diameter	38 mm
Connection thread	M1.4
DIN	2270
Calibration Group	L
Gross Weight	0.131 kg
Product Group	362

EAN

7630041110524