
Subject to modification in technic and design. Errors and omissions exc

Encoders without bearings - incremental

Sensor head with magnetic wheel Max. 4096 pulses per revolution

MIR₁₀



MIR10

Features

- Sensor head with magnetic wheel
- Robust magnetic sensing method
- Max. 4096 pulses per revolution
- Output signals A 90° B with zero pulse
- Output circuits: HTL/push-pull and TTL/RS422
- Non-contact, wear-free sensing system
- High resistance to dirt and vibrations

Technical data - electrical ratings		
Short-circuit proof	Yes	
Pulses per revolution	3204096	
Initializing time	≤50 ms after power on (see general informations)	
Interpolation	10-fold, 20-fold, 32-fold, 64-fold	
Output signals	A+, B+, R+, A-, B-, R-	
Reference signal	Zero pulse, width 90° (zero pulse only with magnet rotor incl. reference magnet)	
Output frequency	≤350 kHz	
System accuracy	Typ. ±0.7° (+20 °C)	
Sensing method	Magnetic	
Output stages	HTL/push-pull TTL/RS422	
Interference immunity	DIN EN 61000-6-2	
Emitted interference	DIN EN 61000-6-4	
Approvals	CE, UL	

Technical data - electrical ratings (HTL)		
Voltage supply 1030 VDC		
Reverse polarity protection	Yes	
Consumption typ.	20 mA (w/o load)	

Technical data - electrical ratings (TTL)		
Voltage supply	5 VDC ±5 %	
Consumption typ.	30 mA (w/o load)	
Recommended cable termination	On control side each channel pair 120 Ohm	


Technical data - mechanical design		
Shaft type	ø643.5 mm (through hollow shaft)	
Dimensions (sensor head)	10 x 15 x 45.5 mm	
Protection DIN EN 60529	IP 66, IP 67	
Operating speed	≤10000 rpm (50 and 64 poles) ≤20000 rpm (up to 36 poles)	
Working distance	0.10.6 mm (axial/radial)	
Material	Housing: zinc diecast, plated	
Operating temperature	-40+85 °C	
Relative humidity	EN 60068-2-78:2010 EN 60068-2-30:2005 93 % condensation permitted	
Resistance	DIN EN 60068-2-6 Vibration 30 g, 10-2000 Hz DIN EN 60068-2-27 Shock 500 g, 6 ms	
Weight approx.	130 g	
Connection	Cable 2 m Cable 0.3 m with connector M12	

Subject to modification in technic and design. Errors and omissions excepted.

Encoders without bearings - incremental


Sensor head with magnetic wheel Max. 4096 pulses per revolution

MIR10



2

Magnetic wheel



* Other bore diameter on request.



3.19 Subject to modification in technic and design. Errors and omissions exce

Encoders without bearings - incremental

Sensor head with magnetic wheel Max. 4096 pulses per revolution

MIR₁₀

Selection of sensor head / magnetic wheel

The pulses are a result of the interpolation factor of the sensor head and the number of poles on the magnetic wheel. The table below shows as an example which sensor head and which magnetic wheel have to be combined in order to achieve a certain number of pulses. Other pulses are available on request.

Sensor head MIR10-S	Magnetic wh	Magnetic wheel MIR10-P			
Interpolation factor	32 poles	36 poles	50 poles	64 poles	
10	320	360	500	640	
20	640	720	1000	1280	
32	1024	1152	1600	2048	
64	2048	2304	3200	4096	

3

18/6/2019 Subject to modification in technic and design. Errors and omissions excepted.

Encoders without bearings - incremental


Sensor head with magnetic wheel Max. 4096 pulses per revolution

MIR₁₀

Accessories		
Connectors and cables		
10146775	Female connector M12, 8-pin, straight, without cable	
11170528	Female connector M12, 8-pin, straight, shielded, 5 m cable (ESG 34FH0500GVS)	
11177375	Female connector M12, 8-pin, straight, shielded, 10 m cable (ESG 34FH1000GVS)	
11091511	Female connector M12, 8-pin, straight, shielded, 20 m cable	

Output signals

With clockwise rotation shown below.



HTL/push-pull
>+Vs -2.2 V
<0.7 V
≤20 mA

Outputs	TTL/RS422
Output level High	>2.4 V
Output level Low	<0.7 V
Load	≤20 mA

General information

Terminal assignment

The initializing time of the sensor is 50 ms. Output signals may not be processed during this time.

	•			
Cable or cable 0.3 m with connector M12				
Connector	Core colour	Signals		
Pin 1	white	0 V		
Pin 2	brown	+Vs		
Pin 3	green	A+		
Pin 4	yellow	A-		
Pin 5	grey	B+		
Pin 6	pink	B-		
Pin 7	blue	R+ (zero pulse)		
Pin 8	red	R- (zero pulse inv.)		
5				




Cable screen: connected to sensor housing or connector M12 and sensor housing.

Cable data: PUR 4 x 2 x 0.14 mm², shielded


Bending radius: >50 mm (fix) / >100 mm (cable chain)

Outer diameter: 6.3 mm

Recommended grounding concept



Rotational or linear direction




Encoders without bearings - incremental


Sensor head with magnetic wheel Max. 4096 pulses per revolution

MIR₁₀


Axial misalignment




Working distance




Angular misalignment





MIR10 without reference magnet



Dimensions








Encoders without bearings - incremental

Sensor head with magnetic wheel Max. 4096 pulses per revolution


MIR10

Magnetic wheel without reference magnet

MIR10-P with 32, 36 poles




MIR10-P with 50, 64 poles




Magnetic wheel with reference magnet

MIR10-P with 32, 36 poles



MIR10-P with 50, 64 poles



6