








### **Model Number**

NBB2-12GM50-E2-C3-V1

#### **Features**

- 2 mm flush
- · 3-wire DC
- Weld Immune
- · Slag repellant coatings

### Connection



# **Pinout**



Wire colors in accordance with EN 60947-5-2

| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue)  |
| 4 | BK | (black) |

### Accessories

BF 12

Date of issue: 2013-01-21 910206\_eng.xml

12:14

2013-01-21

date:

Mounting flange, 12 mm

AB-12

Mounting aid

V1-G

4-pin, M12 female field-attachable connector

V1-W

4-pin, M12 female field-attachable connector


V1-G-OR2M-POC

Female cordset, M12, 4-pin, TPE cable, welding-bead resistant

Female cordset, M12
tant

V1-W-OR2M-POC

### **Dimensions**



# **Technical Data**

| General specifications            |                |          |    |  |  |
|-----------------------------------|----------------|----------|----|--|--|
| Switching element function        |                | PNP      | NO |  |  |
| Rated operating distance          | s <sub>n</sub> | 2 mm     |    |  |  |
| Installation                      |                | flush    |    |  |  |
| Output polarity                   |                | DC       |    |  |  |
| Assured operating distance        | sa             | 0 1.62 m | nm |  |  |
| Reduction factor r <sub>Al</sub>  |                | 0.3      |    |  |  |
| Reduction factor r <sub>Cu</sub>  |                | 0.2      |    |  |  |
| Reduction factor r <sub>304</sub> |                | 0.7      |    |  |  |
| NI II Al                          |                |          |    |  |  |

Nominal ratings

 $\begin{array}{cccc} \text{Operating voltage} & \text{U}_{\text{B}} & \text{10} \dots \text{30 V DC} \\ \text{Switching frequency} & \text{f} & \text{0} \dots \text{1500 Hz} \\ \text{Hysteresis} & \text{H} & \text{typ. 5} \ \% \\ \end{array}$ 

Voltage drop  $U_d \le 3 \text{ V}$ Operating current  $I_L = 0 \dots 200 \text{ mA}$ Off-state current  $I_r = 0 \dots 0.5 \text{ mA typ. } 0.1 \text{ } \mu\text{A} \text{ at } 25 \text{ }^{\circ}\text{C}$ 

 $\begin{array}{lll} \mbox{No-load supply current} & \mbox{I}_0^{} & \leq 15 \ \mbox{mA} \\ \mbox{Operating voltage display} & \mbox{LED, green} \\ \mbox{Switching state indication} & \mbox{Multibel-LED, yellow} \\ \mbox{Mag. Field strength, AC fields} & 200 \ \mbox{mT} \\ \mbox{Mag. Field strength, DC fields} & 200 \ \mbox{mT} \\ \end{array}$ 

Functional safety related parameters

MTTF<sub>d</sub> 2430 a
Mission Time (T<sub>M</sub>) 20 a
Diagnostic Coverage (DC) 0 %

Ambient conditions

Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

Mechanical specifications

Connection type Device connector M12 x 1 , 4-pin Housing material Brass, PTFE coated

Sensing face Ceramic coated Protection degree IP67

Compliance with standards and directives

Standard conformity

Standards EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval CSA approval CCSA us Listed, General Purpose CSA approval CCSAus Listed, General Purpose

Copyright Pepperl+Fuchs

Singapore: +65 6779 9091

fa-info@sg.pepperl-fuchs.com

CCC approval Products with a maximum operating voltage of ≤36 V do not bear a

CCC marking because they do not require approval.