

# SAFETY DATA SHEET

PROFOOD HIGH TEMP 2



Page: 1

Compilation date: 11/07/2018

Revision No: 1

## Section 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**Product name:** PROFOOD HIGH TEMP 2

**Product code:** 665017 and PNCB041

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Use of substance / mixture:** PC24: Lubricants, greases, release products.

### 1.3. Details of the supplier of the safety data sheet

**Company name:** Arctic Hayes Ltd

Unit 11

Glover Way

Leeds

West Yorkshire

LS11 5JP

United Kingdom

**Tel:** +44 (0)113 271 5245 | **Fax:** +44(0)113 271 5779

**Email:** sales@arctic-hayes.com

### 1.4. Emergency telephone number

**Emergency tel:** +44 (0)113 271 5245

(Mon to Fri, 8:30am to 5pm)

## Section 2: Hazards identification

### 2.1. Classification of the substance or mixture

**Classification under CLP:** This product has no classification under CLP.

### 2.2. Label elements

**Label elements:** This product has no label elements.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

[cont...]

# SAFETY DATA SHEET

PROFOOD HIGH TEMP 2

Page: 2

**Eye contact:** Bathe the eye with running water for 15 minutes.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Consult a doctor.

**Inhalation:** Not applicable.

## 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** Not applicable.

**Delayed / immediate effects:** Continuous skin contact may cause skin sensitivity and dermatitis

## 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Not applicable.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

[cont...]

# SAFETY DATA SHEET

PROFOOD HIGH TEMP 2

Page: 3

## 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance.

## 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep away from sources of ignition. Keep container tightly closed.

**Suitable packaging:** Not applicable.

## 7.3. Specific end use(s)

**Specific end use(s):** PC24: Lubricants, greases, release products.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Workplace exposure limits:** No data available.

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Not applicable.

**Respiratory protection:** Respiratory protection not required.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses.

**Skin protection:** Protective clothing.

**Environmental:** No special requirement.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Grease

**Colour:** Off-white

**Odour:** Odourless

**Solubility in water:** Insoluble

**Melting point/range°C:** >150

**Flash point°C:** >200

**Autoflammability°C:** >200

**Relative density:** 0.99

### 9.2. Other information

**Other information:** Not applicable.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

[cont...]

# SAFETY DATA SHEET

PROFOOD HIGH TEMP 2

Page: 4

## 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

## 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

## 10.4. Conditions to avoid

**Conditions to avoid:** Heat. Sources of ignition. Flames.

## 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Toxicity values:** No data available.

### Symptoms / routes of exposure

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** Not applicable.

**Delayed / immediate effects:** Continuous skin contact may cause skin sensitivity and dermatitis

**Other information:** Not applicable.

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable in part only.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** Slightly bioaccumulable.

### 12.4. Mobility in soil

**Mobility:** Insoluble in water. Absorbed only slowly into soil.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

[cont...]

# SAFETY DATA SHEET

PROFOOD HIGH TEMP 2

Page: 5

## 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Recovery operations:** Not applicable.

**Disposal of packaging:** Dispose of as normal industrial waste.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.