

Assembly trolley with CLIP-O-FLEX hook-on system

With support brackets and CLIP-O-FLEX trays

CLIP-O-FLEX®

Application:

Thanks to the flexible and modular CLIP-O-FLEX system, the assembly trolley can be optimally designed and adapted to the individual work sequences in production, assembly, development, training and further education. CLIP-O-FLEX sets your work/storage area or your organisation system with one clip and at the same time gives the highest level of horizontal and vertical flexibility.

Version:

- Solidly welded sheet steel structure with painted multiplex panel, 30 mm stark
- Workbench panel with CLIP-O-FLEX support rails installed on the top of the housing left, right and at the rear
- With fixed support brackets incl. CLIP-O-FLEX trays with hook-in brackets 0/40/80°
- Running gear with 2 fixed wheels and 2 steering rollers, including 1 steering roller with stopper
- Central locking with cylinder lock incl. 2 keys

Advantage:

- Simply remove the trays from the cabinet and hang on the hook-in rails at the side
- Flexible hook-on system with only one hooking movement
- Ergonomic workplace design thanks to different inclines and can be relocated horizontally
- Quick access to work equipment, very clear overview
- Rapid conversion and replacement, highest possible level of mobility, less walking required, optimum use of space



| | |
|---------------------------------------|------------------|
| Art. no. | 50237 171 |
| Height | 958 mm |
| Width | 474 mm |
| Depth | 405 mm |
| Central locking | Yes |
| Lock type | Cylinder lock |
| With sliding handle | Yes |
| Load-carrying capacity | 550 kg |
| Dynamic load-carrying capacity | 225 kg |
| Number of fixed rollers | 2 PCS |
| Number of steering rollers | 2 PCS |
| Material of wheel | Solid rubber |
| Wheel diameter | 100 mm |
| Material | Sheet steel |
| Body colour | Optional |
| Colour of front | Optional |
| Surface | Powder-coated |