

Poliflex fine grinding points with PUR binding

Cylindrical, silicon carbide, green




Application:

For preliminary grinding before polishing steel parts, stainless steel (INOX), titanium, light and non-ferrous metals as well as components for food and kitchen technology. For use on flexible shafts, electrical and pneumatic straight grinders. For achieving a fine, matte grinding pattern.

Advantage:

- Optimum contour following due to high flexibility
- Cool, very soft grinding thanks to open structure and elastic binding
- For achieving a fine, matt grinding finish



Art. no.	69200 015
Brand	PFERD
Manufacturer Part Number	4007220535233
Grid size	80
Head diameter x head length	20 x 30 mm
Shaft diameter x shaft length	6 x 40 mm
Max. rotation speed	14300 rpm
Recommended rotation speed	9500 rpm
Number of pieces per packet	10 PCS
Gross Weight	0.025 kg
Product Group	6AB

EAN

4007220535233