



Figure similar

POWER SUPPLY; PHASES:1; PN(KW):0,24;
 UPRI(V):400-230+/-15; USEC(V DC):24; ISEC(A DC):10; F(HZ):50...60; VECTOR GR./SHIELD WNG.:II0 /0; PROTECTION CL.:I; TA/ISOKL:40 /B; W(%):5; IP00;
 TYPE OF TERMINALS:SCREW/TAB CONNECTION;
 INSTALLATION:SCREW; EN 61558, EN61131-2
 >SAFETY ISOLATING TRANSFORMER<

General technical data:

Product designation		4AV4110-2EB00-0A
product brand name		SIDAC
Vector group		II0
Certificate of suitability		CE
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
• varistor protective wiring		Yes
Operating resource protection class		I
Number of shielding windings		0

Inputs:

Phase number of the inputs		1
Type of current of the inputs		AC
Input voltage		
• _1 Rated value	V	415
• _2 Rated value	V	400
• _3 Rated value	V	385
• _4 Rated value	V	245
• _5 Rated value	V	230
• _6 Rated value	V	215
Electrical input frequency		
• minimum	Hz	50

<ul style="list-style-type: none"> • maximum 	Hz	60
Input voltage		
<ul style="list-style-type: none"> • minimum 	V	193.5
<ul style="list-style-type: none"> • maximum 	V	439.9
Input current		
<ul style="list-style-type: none"> • _1 Rated value 	A	0.85
<ul style="list-style-type: none"> • _2 Rated value 	A	0.89
<ul style="list-style-type: none"> • _3 Rated value 	A	0.92
<ul style="list-style-type: none"> • _4 Rated value 	A	1.46
<ul style="list-style-type: none"> • _5 Rated value 	A	1.54
<ul style="list-style-type: none"> • _6 Rated value 	A	1.65
Type of electrical connection at input for main current circuit		screw-type terminals / tab terminals

Outputs:

Type of current		DC
<ul style="list-style-type: none"> • _1 at output 		
Output voltage		
<ul style="list-style-type: none"> • _1 Rated value 	V	24
Output voltage of the measurement signal at analog output for DC maximum	V	30
Output voltage of the measurement signal at analog output for DC minimum	V	20.4
Output current		
<ul style="list-style-type: none"> • _1 Rated value 	A	10
Type of electrical connection at output for main current circuit		screw-type terminals / tab terminals
Relative residual ripple		
<ul style="list-style-type: none"> • of the output voltage 1 for main current circuit maximum 	%	5

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	40
Protection class IP		IP00

Mechanical data:

Mounting type		screws
Construction form of the iron core		EI 120/52
Width	m	120
Height	m	170
Depth	m	105

Certificates/ approvals:

General Product Approval	Shipping Approval	other
--------------------------	-------------------	-------



[Declaration of Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AV41102EB000A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AV41102EB000A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AV41102EB000A&lang=en

last modified:

16.03.2015