



Halogen Low Voltage

ELC/10H 250W GX5.3 24V 1CT/24

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Product data


General information	
Cap-Base	GX5.3 [GX5.3]
Philips Code	13163
ANSI Code	ELC-10H
LIF Code	A1/259-10H
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Disco/Theatre
Life to 50% Failures (Nom)	1000 h
Light technical	
Color Rendering Index (Nom)	100
Operating and electrical	
Power (Nom)	250 W
Voltage (Nom)	24 V
Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Filament Dimensions WxH	-
Bulb Shape	R50 [R 50mm]
Luminaire design requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C
Pinch Temperature (Max)-DUP(do not use)	400 °C
Working Distance WD	31.7 mm
Product data	
Full product code	871150043686330
Order product name	ELC/10H 250W GX5.3 24V 1CT/24
EAN/UPC - Product	8711500436863
Order code	924913220540
Numerator - Quantity Per Pack	1
Local code description	ELC/10H 250W GX5.3 24V 1CT/24

Halogen Low Voltage

Numerator - Packs per outer box	24
Material Nr. (12NC)	924913220540
Net Weight (Piece)	0.024 kg

Dimensional drawing



ELC/10H 250W GX5.3 24V 1CT/24

Product	D (max)	C (max)
ELC/10H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm

