





VIEW A



REVISION RECORD			
REV	ECN	DESCRIPTION	DATE
△		图面更新	05/05/06
△		增加VDE、CE刻字	02/27/08
△		增加自动化方针	09/24/08
△	10-0329	增加标注尺寸	10/07/10
△	14-0107	黄铜变紫铜, 料号变更; 工频耐压变更为额定冲击电压	12/20/14

Pitch range in mm	Nominal dimension range in mm
over 6	over 30
to 10	to 60
to 15	to 90
to 20	to 120
to 25	to 150
±0.15	±0.25
±0.25	±0.3
±0.3	±0.5
±0.5	±0.7
±1.0	±1.0

- NOTES:
- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
 - 2.PITCH: 5.0MM,POLES: 2-24P
 - 3.RATED VOLTAGE/CURRENT: UL 300V/15A VDE 320V/20A
 - 4.OPERATION TEMPERATURES: -40C-+105C
 - 5.RATED IMPULSE VOLTAGE: 4.0KV
 - 6.INSULATION RESISTANCE: 5000MQ/DC1000V
 - 7.UNDIMENSIONED TOLERANCES:



P.C.B LAYOUT

DETACHED LISTS	
MM (INCH)	FINISH:
.X ±	.X ±
.XX ±	.XX ±
.XXX ±	.XXX ±
ANGLES ± 1°	
THIRD ANGLE PROJECTION	
DRT:Zhuwm 07/24/04	
DO NOT SCALE DRAWING	
SCALE N/A	
SHEET 1/1	

ITEM	NAME OF PART	NO. OF PART	QTY	MATERIAL	NOTES
2	ZEDGV-Pin header Automatic assembly	1007B00340(H)	XX	COPPER	Sn Plated
2	ZEDGV-Pin header Manual assembly	1007B00330(H)	XX	COPPER	Sn Plated
1	ZEDGVC-5.0 Housing	1019A0YXXA(H)	1	PA66	UL94V-0

NAME: DEGSON 宁波高压电子有限公司	
DEGSON® DEGSON ELECTRONICS CO., LTD	
ZEDGVC-5.0-XXP-1Y-00A(H)	
TITLE: ASSEMBLY DRAWING	REV T5
DRAWING NO.: ZEDGVC-5.0-EC01	