

1488991-1 ✓ ACTIVE

MCON Interconnection System

TE Internal #: 1488991-1

MCON Interconnection System, Housing for Female Terminals,
Wire-to-Wire / Wire-to-Device / Wire-to-Board, 3 Position, 4mm [.157in] Centerline

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Housings > MCON, CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **1.2 mm [.047 in]**

Connector System: **Wire-to-Board, Wire-to-Device, Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **4 mm [.157 in]**

[All MCON, CONNECTOR HOUSING \(283\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	3
Number of Rows	1

Body Features

Body Material	PA GF
Primary Product Color	Black

Contact Features

Mating Tab Width	1.2 mm[.047 in]
------------------	-----------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes



Strain Relief	Add By Accessory
---------------	------------------

Mating Alignment Type	Polarized
-----------------------	-----------

Housing Features

Centerline (Pitch)	4 mm [.157 in]
--------------------	----------------

Dimensions

Product Width	26.5 mm [1.043 in]
---------------	--------------------

Product Length	19 mm [.748 in]
----------------	-----------------

Product Height	15.6 mm [.614 in]
----------------	-------------------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
-----------------------------	--

Operating Temperature Range	-40 – 125 °C, -40 – 125 °C [-40 – 257 °F] [-40 – 257 °F]
-----------------------------	--

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP67
----------------------	------

Packaging Features

Packaging Quantity	1
--------------------	---

Packaging Method	Package
------------------	---------

Other

Serviceable	Yes
-------------	-----

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)
--	---



Candidate List Declared Against: JAN 2021 (211)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-M4595-T273
MCON, RECEPTACLE AND TAB




TE Part # 964972-1
EINZELLEITERDICHTNG




TE Part # 963143-1
MQS BLINDSTOPFEN



TE Part # 967056-1
MQS BLINDSTOPFEN4MM











TE Part # 967067-1
MQS SGL WIRE SEAL













TE Part # 967067-2
MQS EINZELLEITDICHT

Also in the Series | **MCON Interconnection System**

			
<p>Automotive Connector Caps & Covers (24)</p>	<p>Automotive Connector Locks & Position Assurance(11)</p>	<p>Automotive Headers(1)</p>	<p>Automotive Housings(288)</p>
			
<p>Automotive Seals & Cavity Plugs(4)</p>	<p>Automotive Terminals(114)</p>	<p>Insertion & Extraction Tools(31)</p>	<p>Other Automotive Connector Accessories(6)</p>

Customers Also Bought

 <p>TE Part #1-1924067-1 MCON, CONNECTOR HOUSING</p>	 <p>TE Part #1-1534150-1 MQS, CONNECTOR HOUSING</p>	 <p>TE Part #1393365-1 GET .64 CONNECTOR SYSTEM, RECEPT AND TAB</p>	 <p>TE Part #1-1419168-1 MARKET 1X6 FEMALE SEALED</p>
 <p>TE Part #1-1355135-1 RETAINER 94P</p>	 <p>TE Part #1-1355134-1 RETAINER 94P</p>	 <p>TE Part #1393449-1 V23540A1000Y452=VERSCHL.26P.</p>	 <p>TE Part #1-1452424-2 BLIND PLUG FOR MCON 1.2 CB (1.</p>
 <p>TE Part #1-1534170-1 MQS ABDECKKAPPE2X5P</p>	 <p>TE Part #NB19044001 RNF-100-1/4-RD-SP</p>		

Documents



Product Drawings

[3POS, MCON 1.2 CB REC 2p TL SEALED](#)

English

[3POS, MCON 1.2 CB REC 2p TL SEALED](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1488991-1_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1488991-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1488991-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MCON Interconnection System](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English