

For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) .038" tinned copper conductors, polyethylene insulation, tinned copper braid shield (93% Coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	7x28	TC - Tinned Copper	.038

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PE - Polyethylene	0.019

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	93

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.033

Overall Cable

Overall Nominal Diameter: 0.244 in.

Pair

Pair Color Code Chart:

Number	Color
1	Clear & Blue

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2092)
Bulk Cable Weight:	37 lbs/1000 ft.
Max. Recommended Pulling Tension:	68 lbs.
Min. Bend Radius/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2092 (300 V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 89272

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
78

Nom. Inductance:

Inductance (µH/ft)
.020

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
19.7

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
9.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.4

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.6
10	2.1
50	5.0
100	7.5
200	11.0
400	16.0

Max. Operating Voltage - UL:

Voltage
300 V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9272 006U1000	1,000 FT	39.000 LB	BLUE, LIGHT		78 OHM TWINAX
9272 006U500	500 FT	20.000 LB	BLUE, LIGHT		78 OHM TWINAX
9272 006100	100 FT	4.500 LB	BLUE, LIGHT		78 OHM TWINAX
9272 0061000	1,000 FT	41.000 LB	BLUE, LIGHT	C	78 OHM TWINAX
9272 006500	500 FT	20.500 LB	BLUE, LIGHT	C	78 OHM TWINAX

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 10-16-2012

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the



9272 Twinax - Twinaxial Cable

product.
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).