


## Thermally conductive foil both sides adhesive

- good thermal characteristics
- double-sided adhesive layers
- replaces mechanical fastenings
- cuttings and cut-outs upon request



art. no.	version	width [mm]	art. no.	version	width [mm]
<b>WLFT 404 R25</b>	running metre	25	<b>WLFT 405 R25</b>	running metre	25
<b>WLFT 404 R50</b>	running metre	50	<b>WLFT 405 R50</b>	running metre	50
<b>WLFT 404 R100</b>	running metre	100	<b>WLFT 405 R100</b>	running metre	100
<b>WLFT 404 R200</b>	running metre	200	<b>WLFT 405 R200</b>	running metre	200

art. no.	version	dimensions [mm]	art. no.	version	dimensions [mm]
<b>WLFT 404 100x100</b>	plate	100 x 100	<b>WLFT 405 100x100</b>	plate	100 x 100
<b>WLFT 404 100x200</b>	plate	100 x 200	<b>WLFT 405 100x200</b>	plate	100 x 200
<b>WLFT 404 200x200</b>	plate	200 x 200	<b>WLFT 405 200x200</b>	plate	200 x 200

### Technical data

	<b>WLFT 404</b>	<b>WLFT 405</b>
<b>description</b>	isolations, double-sided adhesive	non isolations, double-sided adhesive
<b>complete thickness</b>	0.127 ( $\pm 0.03$ ) mm	0.15 ( $\pm 0.03$ ) mm
<b>truss material</b>	polyimide (kapton MT) 0.025 mm	aluminum foil 0.05 mm
<b>glue layer</b>	acrylate (pressure sensitive) double-sided	acrylate (pressure sensitive) double-sided
<b>specific thermal resistance</b>	3.7 °C cm <sup>2</sup> /W	3.4 °C cm <sup>2</sup> /W
<b>thermal conductivity</b>	0.37 W/mK	0.5 W/mK
<b>snap through stability</b>	5 KV/mm	–
<b>holding force (overlapping)</b>	0.86 MPa	0.93 MPa
<b>holding force (shear rate)</b>	<b>Al</b> 25 °C 0.897 [MPa]/ <b>Al</b> 150 °C 0.345 [MPa]/ <b>Cu</b> 25 °C 0.828 [MPa]/ <b>Cu</b> 150 °C 0.31 [MPa]/ <b>Al<sub>2</sub>O<sub>3</sub></b> 25 °C 1.17 [MPa]/ <b>Al<sub>2</sub>O<sub>3</sub></b> 150 °C 0.34 [MPa]	<b>Al</b> 25 °C 0.86 [MPa]/ <b>Al</b> 150 °C 0.38 [MPa]/ <b>Cu</b> 25 °C 1.1 [MPa]/ <b>Cu</b> 150 °C 0.48 [MPa]/ <b>Al<sub>2</sub>O<sub>3</sub></b> 25 °C 1.0 [MPa]/ <b>Al<sub>2</sub>O<sub>3</sub></b> 150 °C 0.41 [MPa]
<b>temperature range</b>	-40 °C ... +150 °C	-40 °C ... +150 °C
<b>flammability</b>	UL 94 V-0	UL 94 V-0

**E 5**

Profiles for PCB components  
Heatsinks for PCB  
Profiles for PCB mounting  
Heatsinks for transistors

→ A 89  
→ A 87 – 89  
→ A 87 – 108  
→ C 4 – 9

Finger-shaped heatsinks  
Distance sleeves  
Spacers  
GEL thermal conductive foil

→ C 2 – 3  
→ E 23 – 28  
→ E 29 – 30  
→ E 7