LM9076

LM9076 150mA Ultra-Low Quiescent Current LDO Regulator with Delayed Reset
Output



Literature Number: SNVS260K



LM9076

150mA Ultra-Low Quiescent Current LDO Regulator with Delayed Reset Output

General Description


The LM9076 is a $\pm 3\%$, 150 mA logic controlled voltage regulator. The regulator features an active low delayed reset output flag which can be used to reset a microprocessor system at turn-ON and in the event that the regulator output voltage falls below a minimum value. An external capacitor programs a delay time interval before the reset output pin can return high.

Designed for automotive and industrial applications, the LM9076 contains a variety of protection features such as thermal shutdown, input transient protection and a wide operating temperature range. The LM9076 uses an PNP pass transistor which allows low drop-out voltage operation.

Features


- Available with 5.0V or 3.3V output voltage
- Ultra Low Ground Pin Current, 25 μA typical for 100 μA load
- V_{OUT} initial accuracy of ±1.5%
- V_{OUT} accurate to ±3% over Load and Temperature Conditions
- Low Dropout Voltage, 200 mV typical with 150 mA load
- Low Off State Ground Pin current for LM9076BMA
- Delayed RESET output pin for low V_{OUT} detection
- +70V/-50V Voltage Transients
- Operational V_{IN} up to +40V

Typical Applications




LM9076S-x.x in 5 lead TO-263 package

20083029




LM9076BMA-x.x in 8 lead SO package

Connection Diagrams



Top View
Part Numbers LM9076S-3.3 and LM9076S-5.0
See NS TO-263 Package Number TS5



Top View
Part Numbers LM9076BMA-3.3 and LM9076BMA-5.0
See NS SOIC Package Number M08A

Ordering Information

Output Voltage	Package Type	Order Number	Package Marking	Shipped As
	TO-263-5	LM9076S-3.3	LM9076S-3.3	Rail of 45
2.2		LM9076SX-3.3	LM9076S-3.3	Tape and Reel of 500
3.3	SO-8	LM9076BMA-3.3	9076B MA3.3	Rail of 95
		LM9076BMAX-3.3	9076B MA3.3	Tape and Reel of 2500
5.0	TO-263-5	LM9076S-5.0	LM9076S-5.0	Rail of 45
		LM9076SX-5.0	LM9076S-5.0	Tape and Reel of 500
	SO-8	LM9076BMA-5.0	9076BMA5.0	Rail of 95
		LM9076BMAX-5.0	9076BMA5.0	Tape and Reel of 2500

Absolute Maximum Ratings (Note 1)

V_{IN}(DC) -15V to +55V +70V

V_{IN}(+Transient) t< 10ms, Duty Cycle

V_{IN}(-Transient) t< 1ms, Duty Cycle

SHUTDOWN Pin -15V to +52V **RESET** Pin -0.3V to 20V

-0.3V to V_{OUT} +0.3V C_{DELAY} Pin Storage Temperature -65°C to +150°C

Junction Temperature (T,) +175C ESD, HBM, per AEC - Q100 - 002 +/-2 kV ESD, MM, per AEC - Q100 - 003 +/-250V

Operating Ratings (Note 1)

 V_{IN} Pin 5.35V to 40V V_{SHUTDOWN} Pin 0V to 40V Junction Temperature -40°C < T_{.1} < +125°C

Thermal Resistance TS5B (Note 6)

75°C/W θјс 2.9°C/W

Thermal Resistance M08A (Note 6)

156°C/W θјс 59°C/W

Electrical Characteristics for LM9076-3.3

-50V

The following specifications apply for V_{IN} = 14V; I_{LOAD} = 10 mA; T_J = +25C; C_{OUT} = 10 μ F, 0.5 Ω < ESR < 4.0 Ω ; unless otherwise specified. Bold values indicate -40°C ≤ T₁ ≤ +125°C.(Notes 5, 4) Minimum and Maximum limits are guaranteed through test, design or statistical correlation.

Symbol	Parameter	Conditions	Min	Тур	Max	Units
LM9076-3.3 REGULATOR	CHARACTERISTICS					
	Output Voltage		3.251	3.30	3.349	V
		-20°C ≤ T _J ≤ 85°C 1 mA ≤ I _{LOAD} ≤ 150 mA	3.234	3.30	3.366	V
		$1 \text{mA} \le I_{\text{LOAD}} \le 150 \text{ mA}$	3.201	3.30	3.399	V
V_{OUT}		$V_{IN} = 60V$, $R_{LOAD} = 1 \text{ k}\Omega$, $t \le 40\text{ms}$	2.970	3.30	3.630	V
	Output Voltage Off LM9076 BMA only	$V_{SHUTDOWN} \ge 2V$, $R_{LOAD} = 1 \text{ k}\Omega$	1	0	250	mV
	Reverse Battery	$V_{IN} = -15V,$ $R_{LOAD} = 1 \text{ k}\Omega$	-300	0	-	mV
	Line Regulation	$9.0V \le V_{IN} \le 16V$, $I_{LOAD} = 10 \text{ mA}$	-	4	25	mV
ΔV_{OUT}		$16V \le V_{IN} \le 40V,$ $I_{LOAD} = 10 \text{ mA}$	-	17	35	mV
	Load Regulation	1 mA ≤ I _{LOAD} ≤ 150 mA	-	42	60	mV
	Dropout Voltage	I _{LOAD} = 10 mA	-	30	50	mV
V_{DO}		I _{LOAD} = 50 mA	-	80	_	mV
		I _{LOAD} = 150 mA	-	150	250	mV
	Ground Pin Current	$9V \le V_{IN} \le 16V$, $I_{LOAD} = 100 \text{ uA}$	-	25	45	μΑ
ı		$9V \le V_{IN} \le 40V$, $I_{LOAD} = 10 \text{ mA}$	ı	125	160	μA
I_GND		$9V \le V_{IN} \le 40V$, $I_{LOAD} = 50 \text{ mA}$	I	0.6	-	mA
		$9V \le V_{IN} \le 16V$, $I_{LOAD} = 150 \text{ mA}$	-	3.6	4.5	mA
I _{SC}	V _{OUT} Short Circuit Current	$V_{IN} = 14V,$ $R_{LOAD} = 1\Omega$	200	400	750	mA

Symbol	Parameter	Conditions	Min	Тур	Max	Units
PSRR	Ripple Rejection	$V_{IN} = (14V_{DC}) + (1V_{RMS})$ @ 120Hz) $I_{LOAD} = 50 \text{ mA}$	50	60	-	dB
ESET PIN CHARACTI	ERISTICS	•	•	•		-
V _{OR}	Minimum V _{IN} for valid RESET Status	(Note 3)	_	1.3	2.0	V
V_{THR}	V _{OUT} Threshold for RESET Low	(Note 3)	0.83	0.89	0.94	X V _{OUT} (Nom)
V _{OH}	RESET pin high voltage	External pull-up resistor to $V_{OUT} = 100 \text{ k}\Omega$	V _{OUT} X 0.90	V _{OUT} X 0.99	V _{OUT}	V
V_{OL}	RESET pin low voltage	C _{DELAY} < 4.0V, I _{SINK} = 250 μA	-	0.2	0.3	V
D _{DELAY} PIN CHARACTE	ERISTICS		-			
I _{DELAY}	C _{DELAY} Charging Current	$V_{IN} = 14V,$ $V_{DELAY} = 0V$	-0.70	-0.42	-0.25	uA
V_{OL}	C _{DELAY} pin low voltage	$V_{OUT} < 4.0V,$ $I_{SINK} = I_{DELAY}$	-	0.100	-	V
[†] DELAY	Reset Delay Time	$V_{IN} = 14V, C_{DELAY} = 0.001 \text{ uF}$ V_{OUT} rising from 0V, Δt from $V_{OUT} > V_{OR}$ to RESET pin HIGH	4.7	7.8	13.2	ms

Electrical Characteristics for LM9076-5.0

The following specifications apply for V_{IN} = 14V; $V_{SHUTDOWN}$ = Open; I_{LOAD} = 10 mA; T_J = +25°C; C_{OUT} = 10 μ F, 0.5 Ω < ESR < 4.0 Ω ; unless otherwise specified. **Bold Values indicate** -40°C $\leq T_J \leq$ 125°C. (Note 4), (Note 5) Minimum and Maximum limits are guaranteed through test, design, or statistical correlation.

Symbol	Parameter	Conditions	Min	Тур	Max	Units
LM9076-5.0 REGULATOR	CHARACTERISTICS					-
			4.925	5.00	5.075	V
		-20°C ≤ T _J ≤ 85°C 1 mA ≤ I _{LOAD} ≤ 150 mA	4.900	5.00	5.100	V
	Output Voltage	$1 \text{ mA} \le I_{\text{LOAD}} \le 150 \text{ mA}$	4.850	5.00	5.150	V
V_OUT		V _{IN} = 60V,	4.500	5.00	5.500	V
	Output Voltage Off	$R_{LOAD} = 1 \text{ k}\Omega, \text{ t} \le 40 \text{ms}$ $V_{SHUTDOWN} \ge 2V,$				
	LM9076 BMA only	$R_{LOAD} = 1 \text{ k}\Omega$	-	0	250	mV
	Reverse Battery	$V_{IN} = -15V,$ $R_{LOAD} = 1 \text{ k}\Omega$	-300	0	-	mV
	Line Regulation	$9.0V \le V_{IN} \le 16V$, $I_{LOAD} = 10 \text{ mA}$	-	4	25	mV
ΔV_{OUT}	Line Regulation	$16V \le V_{IN} \le 40V,$ $I_{LOAD} = 10 \text{ mA}$	-	17	35	mV
	Load Regulation	1 mA ≤ I _{LOAD} ≤ 150 mA	-	42	60	mV
	Dropout Voltage	I _{LOAD} = 10 mA	_	30	50	mV
V_{DO}		I _{LOAD} = 50 mA	-	80	-	mV
		I _{LOAD} = 150 mA	-	150	250	mV
	Ground Pin Current	$9V \le V_{IN} \le 16V,$ $I_{LOAD} = 100 \text{ uA}$	-	25	45	μА
		$9V \le V_{IN} \le 40V,$ $I_{LOAD} = 10 \text{ mA}$	-	125	160	μА
I_GND		$9V \le V_{IN} \le 40V,$ $I_{LOAD} = 50 \text{ mA}$	-	0.6	_	mA
		$9V \le V_{IN} \le 16V$, $I_{LOAD} = 150 \text{ mA}$	_	3.6	4.5	mA
	Ground Pin Current in Shutdown Mode	$9V \le V_{IN} \le 40V$, $V_{SHUTDOWN} = 2V$	-	15	25	μА
I _{sc}	V _{OUT} Short Circuit Current	$V_{IN} = 14V,$ $R_{LOAD} = 1\Omega$	200	400	750	mA
PSRR	Ripple Rejection	$V_{IN} = (14V_{DC}) + (1V_{RMS})$ @ 120Hz) $I_{LOAD} = 50 \text{ mA}$	50	60	-	dB
RESET PIN CHARACTERIS	STICS					
V_{OR}	Minimum V _{IN} for valid RESET Status	(Note 3)	-	1.3	2.0	V
V_THR	V _{OUT} Threshold for RESET Low	(Note 3)	0.83	0.89	0.94	X V _{OUT} (Nom)
V_{OH}	RESET pin high voltage	External pull-up resistor to $V_{OUT} = 100 \text{ k}\Omega$	V _{OUT} X 0.90	V _{OUT} X 0.99	V _{OUT}	V
V _{OL}	RESET pin low voltage	$C_{DELAY} < 4.0V,$ $I_{SINK} = 250 \mu A$	-	0.2	0.3	V
C _{DELAY} PIN CHARACTERIS	TICS					

Symbol	Parameter	Conditions	Min	Тур	Max	Units
I _{DELAY}	C _{DELAY} Charging Current	$V_{IN} = 14V,$ $V_{DELAY} = 0V$	-0.70	-0.42	-0.25	uA
V _{OL}	C _{DELAY} pin low voltage	$V_{OUT} < 4.0V,$ $I_{SINK} = I_{DELAY}$	_	0.100	-	V
t _{DELAY}	Reset Delay Time	$V_{\text{IN}} = 14V, C_{\text{DELAY}} = 0.001 \text{ uF}$ V_{OUT} rising from 0V, Δt from $V_{\text{OUT}} > V_{\text{OR}}$ to RESET pin HIGH	7.1	11.9	20.0	ms
SHUTDOWN CONTROL LO	GIC — LM9076BMA-5.0	Only				
V _{IL(SD)}	SHUTDOWN Pin Low Threshold Voltage	V _{SHUTDOWN} pin falling from 5.0V until V _{OUT} >4.5V (V _{OUT} = On)	1	1.5	-	V
V _{IH(SD)}	SHUTDOWN Pin High Threshold Voltage	$V_{SHUTDOWN}$ pin rising from 0V until $V_{OUT} < 0.5V$ ($V_{OUT} = Off$)	-	1.5	2	V
	SHUTDOWN Pin High Bias Current	V _{SHUTDOWN} = 40V	-	35	_	μΑ
I _{IH(SD)}		V _{SHUTDOWN} = 5V	_	15	35	μA
		V _{SHUTDOWN} = 2V	-	6	10	μΑ
I _{IL(SD)}	SHUTDOWN Pin Low Bias Current	V _{SHUTDOWN} = 0V	-	0	_	μΑ

Note 1: Absolute Maximum Ratings indicate the limits beyond which the device may cease to function, and/or damage to the device may occur.

Note 2: Operating Ratings indicate conditions for which the device is intended to be functional, but does not guarantee specific performance limits. For guaranteed specifications and conditions refer to the Electrical Characteristics

Note 3: Not Production tested, Guaranteed by Design. Minimum, Typical, and/or Maximum values are provided for informational purposes only.

Note 4: Pulse testing used maintain constant junction temperature (T_J).

Note 5: The regulated output voltage specification is not guaranteed for the entire range of V_{IN} and output loads. Device operational range is limited by the maximum junction temperature (T_J). The junction temperature is influenced by the ambient temperature (T_A), package selection, input voltage (V_{IN}), and the output load current. When operating with maximum load currents the input voltage and/or ambient temperature will be limited. When operating with maximum input voltage the load current and/or the ambient temperature will be limited.


Note 6: Worst case (FREE AIR) per EIA/JESD51-3.

Typical Performance Characteristics


Output Capacitor ESR 30 C_{OUT} = 10 μF T_A = 25°C OUTPUT CAPACITOR ESR (Ω) 10 3 STABLE REGION 0.3 0.1 0 25 50 75 100 125 150 LOAD CURRENT (mA)

Output Voltage vs Low Input Voltage


20083031



Ground Pin Current vs Low Input Voltage




Output Capacitor ESR




20083032

Output Voltage vs Low Input Voltage




20083034


Ground Pin Current vs Low Input Voltage




Ground Pin Current vs Load Current




Output Voltage vs Input Voltage




Output Voltage vs Junction Temperature




Ground Pin Current vs Load Current






Output Voltage vs Junction Temperature




20083042

Dropout Voltage vs Load Current




20083043

Load Transient Response




20083045

Line Transient Response




Load Transient Response




20083044

Line Transient Response



20083046

Delayed Reset Time vs Vin



Ripple Rejection 80 V_{IN} = 14V ||| | I_{LOAD} = 10 mA C_{OUT} = 10 μF 70 RIPPLE REJECTION (dB) 60 50 40 30 20 10 10 10k 100k 1M 100 1k FREQUENCY (Hz) 20083051

Application Information

REGULATOR BASICS

The LM9076 regulator is suitable for Automotive and Industrial applications where continuous connection to a battery supply is required (refer to the Typical Application circuit).

The pass element of the regulator is a PNP device which requires an output bypass capacitor for stability. The minimum bypass capacitance for the output is 10 μ F (refer to ESR limitations). A 22 μ F, or larger, output bypass capacitor is recommended for typical applications

INPUT CAPACITOR

The LM9076 requires a low source impedance to maintain regulator stability because critical portions of the internal bias circuitry are connected to directly to $V_{\rm IN}.$ In general, a 10 μF electrolytic capacitor, located within two inches of the LM9076, is adequate for a majority of applications. Additionally, and at a minimum, a 0.1 μF ceramic capacitor should be located between the LM9076 $V_{\rm IN}$ and Ground pin, and as close as is physically possible to the LM9076 itself .

OUTPUT CAPACITOR

An output bypass capacitor is required for stability. This capacitance must be placed between the LM9076 V_{OUT} pin and Ground pin, as close as is physically possible, using traces that are not part of the load current path.

The output capacitor must meet the requirements for minimum capacitance and also maintain the appropriate ESR value across the entire operating ambient temperature range. There is no limit to the maximum output capacitance as long as ESR is maintained.

The minimum bypass capacitance for the output is 10 μ F (refer to ESR limitations). A 22 μ F, or larger, output bypass capacitor is recommended for typical applications.

Solid tantalums capacitors are recommended as they generally maintain capacitance and ESR ratings over a wide temperature range. Ceramic capacitor types XR7 and XR5 may be used if a series resistor is added to simulate the minimum ESR requirement. See *Figure 1*.

Aluminum electrolytic capacitors are not recommended as they are subject to wide changes in capacitance and ESR across temperature.




FIGURE 1. Using Low ESR Capacitors

DELAY CAPACITOR

The capacitor on the Delay pin must be a low leakage type since the charge current is minimal (420 nA typical) and the pin must fully charge to $V_{\rm OUT}$. Ceramic, Mylar, and polystyrene capacitor types are generally recommended, although changes in capacitance values across temperature changes will have some effect on the delay timing.

Any leakage of the $I_{\rm DELAY}$ current, be it through the delay capacitor or any other path, will extend the delay time, possibly to the point that the Reset pin output does not go high.

SHUTDOWN PIN - LM9076BMA ONLY

The basic On/Off control of the regulator is accomplished with the SHUTDOWN pin. By pulling the SHUTDOWN pin high the regulator output is switched Off. When the regulator is switched Off the load on the battery will be primarily due to the SHUTDOWN pin current.

When the SHUTDOWN pin is low, or left open, the regulator is switched On. When an unregulated supply, such as V BATTERY , is used to pull the SHUTDOWN pin high a series resistor in the range of $10 K\Omega$ to $50 K\Omega$ is recommended to provide reverse voltage transient protection of the SHUTDOWN pin. Adding a small capacitor (0.001uF typical) from the SHUTDOWN pin to Ground will add noise immunity to prevent accidental turn on due to noise on the supply line.

RESET FLAG

The $\overline{\text{RESET}}$ pin is an open collector output which requires an external pull-up resistor to develop the reset signal. The external pull-up resistor should be in the range of 10 k Ω to 200 k Ω .

At V_{IN} values of less than typically 2V the \overline{RESET} pin voltage will be high. For V_{IN} values between typically 2V and approximately $V_{OUT} + V_{BE}$ the \overline{RESET} pin voltage will be low. For V_{IN} values greater than approximately $V_{OUT} + V_{BE}$ the \overline{RESET} pin voltage will be dependent on the status of the V_{OUT} pin voltage and the Delayed Reset circuitry. The value of V_{BE} is typically 600 mV at 25°C and will decrease approximately 2 mV for every 1°C increase in the junction temperature. During normal operation the \overline{RESET} pin voltage will be high .

Any load condition that causes the $V_{\rm OUT}$ pin voltage to drop below typically 89% of normal will activate the Delayed Reset circuit and the $\overline{\rm RESET}$ pin will go low for the duration of the delay time.

Any line condition that causes V_{IN} pin voltage to drop below typically $V_{OUT} + V_{BE}$ will cause the \overline{RESET} pin to go low without activating the Delayed Reset circuitry.

Excessive thermal dissipation will raise the junction temperature and could activate the Thermal Shutdown circuitry which, in turn, will cause the $\overline{\text{RESET}}$ pin to go low.

For the LM9076BMA devices, pulling the SHUTDOWN pin high will turn off the output which, in turn, will cause the $\overline{\text{RE-}}$ pin to go low once the V_{OUT} voltage has decayed to a value that is less than typically 89% of normal. See *Figure 2*.

RESET DELAY TIME

When the regulator output is switched On, or after recovery from brief V_{OUT} fault condition, the $\overline{\text{RESET}}$ flag can be can be programmed to remain low for an additional delay time. This will give time for any system reference voltages, clock signals, etc., to stabilize before the micro-controller resumes normal operation.

This delay time is controlled by the capacitor value on the C_{DELAY} pin. During normal operation the C_{DELAY} capacitor is charged to near V_{OUT} . When a V_{OUT} fault causes the \overline{RE} -SET pin to go low, the C_{DELAY} capacitor is quickly discharged to ground. When the V_{OUT} fault is removed, and V_{OUT} returns to the normal operating value, the C_{DELAY} capacitor begins charging at a typical constant 0.420 uA rate. When the voltage on the C_{DELAY} capacitor reaches the same potential as the V_{OUT} pin the \overline{RESET} pin will be allowed to return high.

The typical $\overline{\text{RESET}}$ delay time can be calculated with the following formula:

$$t_{DELAY} = V_{OUT} X (C_{DELAY} / I_{DELAY})$$

For the LM9076–3.3 with a C_{DELAY} value of 0.001 uF and a I_{DELAY} value of 0.420 uA the typical \overline{RESET} delay time is:

$$t_{DELAY} = 3.3V \times (0.001 \text{ uF} / 0.420 \text{ uA}) = 7.8 \text{ ms}$$

For the LM9076–5.0 with a C_{DELAY} value of 0.001 uF and a I_{DELAY} value of 0.420 uA the typical \overline{RESET} delay time is:

$$t_{DELAY} = 5.0V X (0.001uF / 0.420uA) = 11.9 ms$$

THERMAL PROTECTION

Device operational range is limited by the maximum junction temperature (T_J) . The junction temperature is influenced by the ambient temperature (T_A) , package selection, input volt-

age (V_{IN}) , and the output load current. When operating with maximum load currents the input voltage and/or ambient temperature will be limited. When operating with maximum input voltage the load current and/or the ambient temperature will be limited.

Even though the LM9076 is equipped with circuitry to protect itself from excessive thermal dissipation, it is not recommended that the LM9076 be operated at, or near, the maximum recommended die junction temperature (T_J) as this may impair long term device reliability.

The thermal protection circuity monitors the temperature at the die level. When the die temperature exceeds typically 160°C the voltage regulator output will be switched off.






FIGURE 2. Typical Reset Pin Operational Waveforms

Physical Dimensions inches (millimeters) unless otherwise noted



5-Lead TO-263 NS Package Number TS5B



8-Lead (0.150" Wide) Molded SO Package NS Package Number M08A

Notes

For more National Semiconductor product information and proven design tools, visit the following Web sites at:

Pr	oducts	Design Support		
Amplifiers	www.national.com/amplifiers	WEBENCH	www.national.com/webench	
Audio	www.national.com/audio	Analog University	www.national.com/AU	
Clock Conditioners	www.national.com/timing	App Notes	www.national.com/appnotes	
Data Converters	www.national.com/adc	Distributors	www.national.com/contacts	
Displays	www.national.com/displays	Green Compliance	www.national.com/quality/green	
Ethernet	www.national.com/ethernet	Packaging	www.national.com/packaging	
Interface	www.national.com/interface	Quality and Reliability	www.national.com/quality	
LVDS	www.national.com/lvds	Reference Designs	www.national.com/refdesigns	
Power Management	www.national.com/power	Feedback	www.national.com/feedback	
Switching Regulators	www.national.com/switchers			
LDOs	www.national.com/ldo			
LED Lighting	www.national.com/led			
PowerWise	www.national.com/powerwise			
Serial Digital Interface (SDI)	www.national.com/sdi			
Temperature Sensors	www.national.com/tempsensors			
Wireless (PLL/VCO)	www.national.com/wireless			

THE CONTENTS OF THIS DOCUMENT ARE PROVIDED IN CONNECTION WITH NATIONAL SEMICONDUCTOR CORPORATION ("NATIONAL") PRODUCTS. NATIONAL MAKES NO REPRESENTATIONS OR WARRANTIES WITH RESPECT TO THE ACCURACY OR COMPLETENESS OF THE CONTENTS OF THIS PUBLICATION AND RESERVES THE RIGHT TO MAKE CHANGES TO SPECIFICATIONS AND PRODUCT DESCRIPTIONS AT ANY TIME WITHOUT NOTICE. NO LICENSE, WHETHER EXPRESS, IMPLIED, ARISING BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT.

TESTING AND OTHER QUALITY CONTROLS ARE USED TO THE EXTENT NATIONAL DEEMS NECESSARY TO SUPPORT NATIONAL'S PRODUCT WARRANTY. EXCEPT WHERE MANDATED BY GOVERNMENT REQUIREMENTS, TESTING OF ALL PARAMETERS OF EACH PRODUCT IS NOT NECESSARILY PERFORMED. NATIONAL ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR BUYER PRODUCT DESIGN. BUYERS ARE RESPONSIBLE FOR THEIR PRODUCTS AND APPLICATIONS USING NATIONAL COMPONENTS. PRIOR TO USING OR DISTRIBUTING ANY PRODUCTS THAT INCLUDE NATIONAL COMPONENTS, BUYERS SHOULD PROVIDE ADEQUATE DESIGN, TESTING AND OPERATING SAFEGUARDS.

EXCEPT AS PROVIDED IN NATIONAL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, NATIONAL ASSUMES NO LIABILITY WHATSOEVER, AND NATIONAL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY RELATING TO THE SALE AND/OR USE OF NATIONAL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS PRIOR WRITTEN APPROVAL OF THE CHIEF EXECUTIVE OFFICER AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

Life support devices or systems are devices which (a) are intended for surgical implant into the body, or (b) support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in a significant injury to the user. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system or to affect its safety or effectiveness.

National Semiconductor and the National Semiconductor logo are registered trademarks of National Semiconductor Corporation. All other brand or product names may be trademarks or registered trademarks of their respective holders.

Copyright© 2007 National Semiconductor Corporation

For the most current product information visit us at www.national.com



National Semiconductor Americas Customer Support Center Email: new.feedback@nsc.com Tel: 1-800-272-9959 National Semiconductor Europe Customer Support Center Fax: 449 (0) 180-530-85-86 Email: europe.support@nsc.com Deutsch Tel: +49 (0) 69 9508 6208 English Tel: +49 (0) 870 24 0 2171 Français Tel: +33 (0) 1 41 91 8790 National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com

National Semiconductor Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products Applications

interface.ti.com

Audio www.ti.com/audio Communications and Telecom www.ti.com/communications **Amplifiers** amplifier.ti.com Computers and Peripherals www.ti.com/computers dataconverter.ti.com Consumer Electronics www.ti.com/consumer-apps **Data Converters DLP® Products** www.dlp.com **Energy and Lighting** www.ti.com/energy DSP dsp.ti.com Industrial www.ti.com/industrial Clocks and Timers www.ti.com/clocks Medical www.ti.com/medical

Logic logic.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Security

Power Mgmt power.ti.com Transportation and Automotive www.ti.com/automotive

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID <u>www.ti-rfid.com</u>
OMAP Mobile Processors <u>www.ti.com/omap</u>

Interface

Wireless Connectivity www.ti.com/wirelessconnectivity

TI E2E Community Home Page <u>e2e.ti.com</u>

www.ti.com/security