

## Cemented carbide milling bit with STEEL toothing

Shank diameter 6 mm



### Application:

Deburring, processing contours, chamfering/rounding edges, milling out for preparation of deposit welds, preparation/levelling of welding seams, fettling, altering geometries.



### Advantage:

- Extremely high cutting performance on steel and cast steel
- Smooth milling properties
- Reduced vibration and less noise

<b>Art. no.</b>	<b>76007 040</b>
<b>Brand</b>	PFERD
<b>Manufacturer Part Number</b>	4007220937235
<b>Form</b>	Cylindrical shape with spur cut
<b>Head diameter x cutting edge length</b>	10 x 20 mm
<b>Cutting edge length</b>	20 mm
<b>Length</b>	60 mm
<b>Serration type</b>	STEEL
<b>Gross Weight</b>	0.032 kg
<b>Product Group</b>	6AB

### EAN

4007220937235