

1192A Multi-Conductor - Four-Conductor Star Quad, Low-Impedance Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (42x40) high-conductivity bare copper conductors, polyethylene insulation, tinned copper braid shield (95% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
4	24	42x40	SBC - Soft Bare Copper	.024

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
PE - Polyethylene	.016	.056

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Blue
2	White
3	Blue w/White Stripe
4	White w/Blue Stripe

Overall Nominal Diameter: 0.245 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 33 lbs/1000 ft.

Max. Recommended Pulling Tension: 21 lbs.

Min. Bend Radius/Minor Axis: 2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

1192A Multi-Conductor - Four-Conductor Star Quad, Low-Impedance Cable

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
40

Nom. Inductance:

Inductance (µH/ft)
.21

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
39.2

Nom. Cap. Between Cond. in a Quad Config.:

Capacitance (pF/ft)
57.4

Nominal Velocity of Propagation:

VP (%)
66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
26.6

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
7.1

Max. Operating Voltage - UL:

Voltage
100 V RMS

Max. Operating Voltage - Other:

Voltage	Description
18.0 kV	Nom. breakdown voltage between conductors
16.9 kV	Nom. breakdown voltage conductors to shield

Max. Recommended Current:

Current
2.9 Amps per conductor @ 25°C

Other Electrical Characteristic 1: 2/c 21 AWG equivalent DCR when connected to a 3-pin XLR

Notes (Overall)

Notes: Quad connection scheme: The two blue wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the two white wires (or remaining wires) are connected together to form the second conductor.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1192A B59N1000	1,000 FT	36.000 LB	BLACK, MATTE	C	4 #24 PE SH PVC BLK MTT
1192A B59100	100 FT	4.100 LB	BLACK, MATTE		4 #24 PE SH PVC BLK MTT
1192A B591000	1,000 FT	36.000 LB	BLACK, MATTE	C	4 #24 PE SH PVC BLK MTT
1192A B59500	500 FT	18.000 LB	BLACK, MATTE	C	4 #24 PE SH PVC BLK MTT
1192A G7V1000	1,000 FT	36.000 LB	RED, MATTE	C	4 #24 PE SH PVC RED MTT
1192A G7WN1000	1,000 FT	36.000 LB	GREEN, MATTE	C	4 #24 PE SH PVC GRN MTT
1192A G7W1000	1,000 FT	36.000 LB	GREEN, MATTE	C	4 #24 PE SH PVC GRN MTT
1192A G7X1000	1,000 FT	36.000 LB	BLUE, MATTE	C	4 #24 PE SH PVC BLU MTT
1192A G7X500	500 FT	18.000 LB	BLUE, MATTE		4 #24 PE SH PVC BLU MTT
1192A G8CN1000	1,000 FT	36.000 LB	PURPLE, MATTE		4 #24 PE SH PVC PUR MTT
1192A G8C1000	1,000 FT	36.000 LB	PURPLE, MATTE		4 #24 PE SH PVC PUR MTT
1192A G8M1000	1,000 FT	36.000 LB	YELLOW, MATTE		4 #24 PE SH PVC YEL MTT
1192A U901000	1,000 FT	36.000 LB	GRAY, MATTE	C	4 #24 PE SH PVC GRY MTT

Notes:

C = CRATE REEL PUT-UP.

1192A Multi-Conductor - Four-Conductor Star Quad, Low-Impedance Cable

Revision Number: 1 Revision Date: 08-01-2013

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).