

Manual forklift, manual hydraulic forklift truck

Carrying capacity 500 and 1000 kg

fetra
Transportgeräte

Application:

for occasional use as a lifting and transport device

Execution:

- Stable section steel construction
- with tubular push handles
- Hydraulic pump with chrome-plated piston and overload valve actuation via drawbar
- Lowering valve via hand lever
- Load centre distance: 585 mm
- 2 castors, polyurethane tyre wheels 150 x 40 mm and 2 polyurethane fork rollers 80 x 70 mm. Castors with locking device.

| | |
|---------------------------------|------------------|
| Art. no. | 50262 504 |
| Brand | FETRA |
| Manufacturer Part Number | 6856 |
| Load-carrying capacity | 1000 kg |
| Length | 1600 mm |
| Width | 794 mm |
| Fork length | 1150 mm |
| Fork arm width | 160 mm |
| Fork, external distance | 540 mm |
| Fork roller diameter | 80 mm |
| Min. lift height | 88 mm |
| Lift height | 1500 mm |
| Material of wheel | Polyurethane |
| Total stop optional | No |
| Gross Weight | 220.000 kg |
| Height | 2010 mm |
| Wheel diameter | 150 mm |
| Wheel width | 40 mm |
| Product Group | 5AE |



EAN

4017976068565

