

P/N: MR07

Revision

30134

Last modified

2015-10-31 13:03 UTC+1

Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>



General description	
Part number	MR07
Part name	Hammer Probe
<p>The FLIR MR07 Hammer Probe expands the functionality of your FLIR moisture meter by allowing you to take measurements in the subfloor through carpet, hardwood flooring, and hard materials that are difficult to penetrate with a standard pin probe.</p> <p>FLIR's new insulated pins are smaller in diameter—requiring minimal force to drive the pins into a surface—resulting in less impact to the material. The sandblasted, hardened-steel pins with a single-piece design prevent bending and create an improved bonding surface for the abrasion-resistant insulation. The insulation extends all the way to the connection to the probe, so even if you drive the pins all the way into the wall cavity, the drywall will not affect the measurement.</p> <ul style="list-style-type: none"> • Insulated pins designed for increased durability. • Rubberized ergonomic grips reduce slippage. • Detachable cord with durable BNC connection. • Pins included: 2 pairs of 2 in. pins. 	

Meter data	
Suitable main unit	MR77, MR160, MR176
Cable length	2.45 m (8 ft.) uncoiled
Included insulated pin pairs and length	2 pairs of 2 in. (50 mm)
Warranty	2 years (with registration)

Meter physical data	
Weight:	1.22 kg (1.10 lbs.)
Dimensions (H x W x L)	4.5 cm x 5.97 cm x 45.4 cm (1.8 in. x 2.4 in. x 17.9 in.)
Material	PC-ABS, stainless steel
Color	Black

Shipping information	
Packaging type	White box with accessory color printing
Packaging contents	MR07, 2 sets of 2 in. insulated pins, pin wrench, shoulder case
Packaging weight	5 kg (11.1 lb.)
Packaging dimensions (H x W x L)	15.5 cm x 18 cm x 65 cm (6.1 in. x 7.1 in. x 25.6 in.)
Master carton weight	11 kg (24.25 lb.)
Master carton dimensions (H x W x L)	18.5 cm x 36.5 cm x 67 cm (7.3 in. x 14.4 in. x 26.4 in.)
Master carton quantity	2
EAN-13	0793950370070
UPC-12	793950370070