

Material Safety Data Sheet

1. Chemical Product and Company Identification

DESCRIPTION: Shockproof 24 Hour Wall Clock 225mm
PRODUCT TYPE: 6580141

- **Manufacturer/Supplier Information**

MSDS Prepared by:

Yiwu Minoxing Electronics Factory
ADD: International Trade City G3-1842 Yiwu city,
Zhejiang ,China

2. Composition, Information on Ingredients

Chemical Name	CAS#	% by Weight
GLASS FIBER	65997-17-3	46%
PS	9003-53-6	16%
pp	9003-07-0	38%

3. Hazards Identification

3.1 Emergency Overview

Appearance Plastic, glass, mixed colors
Odor N/A
CAUTION!
Not a significant fire hazard.

- **HMIS Rating**

HEALTH = 0 (slight)
FLAMMABILITY = 0 (minimal)
REACTIVITY = 0 (minimal)

3.2 Potential Health Effects

- **Immediate Hazards**

INGESTION: Not expected to be harmful under normal conditions of use.
INHALATION: Not expected to be harmful under normal conditions of use. However, if allowed to become airborne, may cause irritation of nose, throat and lungs.
SKIN: Not expected to be harmful under normal conditions of use.
EYES: Not expected to be harmful under normal conditions of use.

- **Delayed Hazards**

None of the components present in this product at concentrations equal to or greater than 0.1% have been listed by NTP, classified by IARC, nor regulated by OSHA as a carcinogen.

4. First Aid Measures

INGESTION: N/A
INHALATION: N/A

SKIN: N/A.
EYES: N/A

5. Fire Fighting Measures

Autoignition Temperature	Not available
Upper/Lower Flammable Limits	Not applicable
Up/Lower Explosive Limits, % by Vol	Not applicable
Flash Point	Not applicable

6. Accidental Release Measures

7. Handling and Storage

7.1 Handling

Handle in accordance with good industrial hygiene and safety practices. Always use appropriate Personal Protective Equipment (PPE).

INHALATION: Avoid prolonged or repeated breathing of dust or vapor.

SKIN: n/a

EYES: n/a

7.2 Storage

Keep from moisture.

Store in a cool, dry place.

Keep containers tightly closed.

8. Exposure Controls/Personal Protection

8.1 Exposure Controls

If airborne contaminants are generated when the material is heated or handled, sufficient ventilation in volume and air flow patterns should be provided to keep air contaminant concentration levels below acceptable criteria.

8.2 Personal Protection

Where air contaminants can exceed acceptable criteria, use NIOSH/MSHA approved respiratory protection equipment. Respirators should be selected based on the form and concentration of contaminants in air in accordance with OSHA laws and regulations or other applicable standards or guidelines, including ANSI standards regarding respiratory protection. Use goggles if contact is likely. Wear impervious gloves as required to prevent skin contact.

8.3 Exposure Guidelines

None established

9. Physical and Chemical Properties

Percent Volatiles	n/a
pH @ 25 C	n/a
Specific Gravity	n/a
Appearance	solid
Autoignition Temperature	Not available
Boiling Point	n/a
Evaporation Rate (Butyl Acetate=1)	n/a
Upper/Lower Flammable Limits	Not applicable
Up/Lower Explosive Limits, % by Vol	Not applicable
Flash Point	Not applicable
Freezing Point	n/a
Odor	none
Odor Threshold, ppm	Not available

10. Stability and Reactivity

Normally stable

- **Incompatibilities:**

Oxidizers, acids or bases.

- **Decomposition products may include:**

N/A.

- **Hazardous polymerization:**

Will not occur.

- **Other Hazards:**

None known to company.

11. Toxicological Information

See Section 3 Hazards Identification information.

12. Ecological Information

Not determined.

13. Disposal Considerations

Dispose of according to local, state/provincial, and federal requirements.
