

Circular cutter, type 00

for diameter range from 30-200 mm

Application:


For drilling holes in the diameter range from 30 to 200 mm up to a max. material thickness of 30 mm in steel, non-ferrous metals, seals, rubber, leather and similar materials.

Execution:

- steel circular cutter with cutter holder and cutter, HSS, type 422

Advantage:

- universal use for a multitude of materials
- possible to create cost-effective holes in a large diameter range
- excellent cutting properties and high degree of cutting precision



Art. no.	11350 131
Brand	GFS
Manufacturer Part Number	21 011 002
Type	Type 00 with cutter, type 422 HSSE
Suitable for min. diameter	30 mm
Morse taper size	MK 2
Gross Weight	0.792 kg
Product Group	119