

## PDJN clamp holder, negative, right

For copy turning and longitudinal turning using DN indexable insert

**ATORN**<sup>®</sup>

### Application


For copy turning and longitudinal turning using DN indexable insert 55°.

### Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type D, 93° pitch angle, 55° tip angle, 0° clearance angle

### Advantage

- very slim geometry, optimised for contour turning with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



|                                       |                   |
|---------------------------------------|-------------------|
| <b>Art. No.</b>                       | <b>17838 011</b>  |
| <b>ISO name</b>                       | PDJN R/L 2020 K15 |
| <b>Shaft height</b>                   | 20 mm             |
| <b>Shank width</b>                    | 20 mm             |
| <b>Length</b>                         | 125 mm            |
| <b>Length of head</b>                 | 34 mm             |
| <b>Programming size</b>               | 25 mm             |
| <b>Suitable for indexable inserts</b> | DN.. 1506..       |
| <b>Tool design</b>                    | Right             |
| <b>DIN</b>                            | 4983              |

### EAN-Code

4050293126808