

Horizontal quick-action clamp

With open clamping arm and horizontal base



Application:


For quick clamping of workpieces.

Version:

- Galvanised and passivated
- Ergonomic, oil-resistant handle with large hand rest and soft components.
- Case-hardened and lubricated bearing bushes

Delivery:

With thrust bolt and protective cap



Art. no.	26215 030
Size	3
Hole distance	25.7 mm
Min./max. distance between stop and centre of drill	22-31.8 mm
Bore diameter	6.5 mm
Clamping height	32 mm
Retaining force	1800 N
Max. tensile force	2500 N
Height	48.5 mm
Length 2	206 mm
Thumbscrew size	M8 x 45 mm

EAN-Code

4020772093037