

## Revolving centring point

Slim; centring point with small housing diameter



### Application:

For mounting and supporting long and projecting lathe parts with centre drill hole to avoid imbalance and to encourage stabilisation.

### Execution:

- Tip angle 60°.
- Precision and rough machining of universal components.
- Hardened and ground.
- Moving point can be replaced.

### Advantage:

- Particularly favourable where conditions on the lathe are confined.
- Precision roller bearings ensure a high level of concentricity.

### Delivery:

1x revolving centring point.



|                                     |                  |
|-------------------------------------|------------------|
| <b>Art. no.</b>                     | <b>22132 030</b> |
| <b>Brand</b>                        | RÖHM             |
| <b>Manufacturer Part Number</b>     | 5429             |
| <b>Morse taper size</b>             | MK 3             |
| <b>Programming size</b>             | 62 mm            |
| <b>Programming size for housing</b> | 44 mm            |
| <b>Max. workpiece weight</b>        | 400 kg           |
| <b>Max. rotation speed</b>          | 7000 rpm         |
| <b>Concentricity tolerance</b>      | 0.005 mm         |
| <b>Diameter of housing</b>          | 34 mm            |
| <b>Tip diameter</b>                 | 15 mm            |
| <b>Gross Weight</b>                 | 0.510 kg         |
| <b>Product Group</b>                | 201              |

### EAN

4019208000145