

Printing date 03.06.2020

Version number 302

Revision: 03.06.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier 600237
- · Trade name: PU Foam Remover E-COLL
- · Article number: 4317784234078

### · 1.2 Relevant identified uses of the substance or mixture and uses advised against

- · Sector of Use
- SU21 Consumer uses: Private households / general public / consumers
- SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- · Application of the substance / the mixture Cleaning material/ Detergent
- · 1.3 Details of the supplier of the safety data sheet

#### · Manufacturer/Supplier:

E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH EDE Platz 1 D-42389 Wuppertal Germany

Tel. +49 202 6096-0 e-mail: sdb@ede.de

- Further information obtainable from: Product safety department
- · 1.4 Emergency telephone number: Giftinformationszentrum Mainz Tel.: +49 (6131) 19240

#### **SECTION 2: Hazards identification**

#### · 2.1 Classification of the substance or mixture

· Classification according to Regulation (EC) No 1272/2008

Skin Irrit. 2H315Causes skin irritation.Eye Irrit. 2H319Causes serious eye irritation.

#### · 2.2 Label elements

• Labelling according to Regulation (EC) No 1272/2008 The product is classified and labelled according to the CLP regulation.

· Hazard pictograms



· Signal word Warning

#### Hazard statements

H315 Causes skin irritation. H319 Causes serious eye irritation.



Printing date 03.06.2020

# Safety data sheet according to 1907/2006/EC, Article 31

Version number 302

Revision: 03.06.2020

# Trade name: PU Foam Remover E-COLL

(Contd. of page 1)

· Precautionary statements			
If medical advice is needed, have product container or label at hand.			
Keep out of reach of children.			
Do not breathe vapours.			
Wear protective gloves / eye protection / face protection.			
FIN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.			
IF exposed or concerned: Get medical advice/attention.			
Dispose of contents/container in accordance with local/regional/national/international regulations.			

## · 2.3 Other hazards

### · Results of PBT and vPvB assessment

- · **PBT:** Not applicable.
- · vPvB: Not applicable.

## **SECTION 3: Composition/information on ingredients**

### · 3.2 Chemical characterisation: Mixtures

• Description: Mixture of substances listed below with nonhazardous additions.

# · Dangerous components:

CAS: 141-43-5	2-aminoethanol	<2.5%
EINECS: 205-483-3	Met. Corr.1, H290; Skin Corr. 1B, H314; Eye Dam. 1, H318	
Index number: 603-030-00-8	<ul> <li>Met. Corr.1, H290; Skin Corr. 1B, H314; Eye Dam. 1, H318</li> <li>Acute Tox. 4, H302; Acute Tox. 4, H312; Acute Tox. 4, H332;</li> </ul>	
	STOT SE 3, H335	
	Aquatic Chronic 3, H412	

• Additional information: For the wording of the listed hazard phrases refer to section 16.

## SECTION 4: First aid measures

#### · 4.1 Description of first aid measures

· General information:

Personal protection for the First Aider. Immediately remove any clothing soiled by the product.

· After inhalation:

Supply fresh air. Seek medical treatment in case of complaints.

#### After skin contact: Immediately wash with water and soap and rinse thoroughly. If skin irritation continues, consult a doctor.

## · After eye contact:

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

#### · After swallowing:

Rinse out mouth and then drink plenty of water.



Printing date 03.06.2020

Version number 302

Revision: 03.06.2020

(Contd. of page 2)

#### Trade name: PU Foam Remover E-COLL

Seek immediate medical advice. Induce vomiting only, if affected person is fully conscious.

- · 4.2 Most important symptoms and effects, both acute and delayed Headache
- 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.

## **SECTION 5: Firefighting measures**

#### · 5.1 Extinguishing media

- Suitable extinguishing agents: CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- · For safety reasons unsuitable extinguishing agents: Water with full jet
- **5.2 Special hazards arising from the substance or mixture** In case of fire, the following can be released: Nitrogen oxides (NOx)
- · 5.3 Advice for firefighters
- **Protective equipment:** Do not inhale explosion gases or combustion gases. Wear self-contained respiratory protective device.
- Additional information Collect contaminated fire fighting water separately. It must not enter the sewage system.

## **SECTION 6: Accidental release measures**

- 6.1 Personal precautions, protective equipment and emergency procedures Particular danger of slipping on leaked/spilled product.
- 6.2 Environmental precautions: Do not allow product to reach sewage system or any water course.
- 6.3 Methods and material for containment and cleaning up: Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust). Pick up mechanically.
- 6.4 Reference to other sections
   See Section 7 for information on safe handling.
   See Section 8 for information on personal protection equipment.
   See Section 13 for disposal information.

# **SECTION 7: Handling and storage**

• 7.1 Precautions for safe handling Use only in well ventilated areas. Keep receptacles tightly sealed.

(Contd. on page 4)



Printing date 03.06.2020

Version number 302

Revision: 03.06.2020

### Trade name: PU Foam Remover E-COLL

(Contd. of page 3)

· Information about fire - and explosion protection: No special measures required.

## · 7.2 Conditions for safe storage, including any incompatibilities

- · Storage:
- Requirements to be met by storerooms and receptacles: Provide alkali-resistant floor. Prevent any seepage into the ground. Store only in the original receptacle.
- · Information about storage in one common storage facility: Store away from oxidising agents.
- Further information about storage conditions: Protect from heat and direct sunlight.
- · 7.3 Specific end use(s) No further relevant information available.

## **SECTION 8: Exposure controls/personal protection**

- · Additional information about design of technical facilities: No further data; see item 7.
- · 8.1 Control parameters

#### · Ingredients with limit values that require monitoring at the workplace:

CAS: 141-43-5 2-aminoethanol

IOELV Short-term value: 7.6 mg/m<sup>3</sup>, 3 ppm Long-term value: 2.5 mg/m<sup>3</sup>, 1 ppm Skin

## · DNELs

## CAS: 141-43-5 2-aminoethanol

Inhalative Long term value for employees 3.3 mg/m<sup>3</sup> (humen)

- Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls

#### · Personal protective equipment:

· General protective and hygienic measures:

Wash hands before breaks and at the end of work. Do not inhale gases / fumes / aerosols. Keep away from foodstuffs, beverages and feed. Immediately remove all soiled and contaminated clothing Avoid contact with the eyes and skin.

Respiratory protection: Use suitable respiratory protective device in case of insufficient ventilation. Short term filter device: Filter A/P2

(Contd. on page 5)



Printing date 03.06.2020

Version number 302

Revision: 03.06.2020

## Trade name: PU Foam Remover E-COLL

(Contd. of page 4)

· Protection of hands:



Protective gloves

# Material of gloves

Butyl rubber, BR Recommended thickness of the material:  $\geq 0.4$  mm

## · Penetration time of glove material

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

### · Eye protection: Recommendation: safety glasses with side protection shield

Body protection: Protective work clothing

## **SECTION 9: Physical and chemical properties**

## · 9.1 Information on basic physical and chemical properties

· General Information

<ul> <li>Appearance:</li> <li>Form:</li> <li>Colour:</li> <li>Odour:</li> <li>Odour threshold:</li> </ul>	Pasty Colourless Characteristic Not determined.	
· pH-value at 20 °C:	10.7	
<ul> <li>Change in condition Melting point/freezing point: Initial boiling point and boiling range</li> </ul>	Undetermined. : Undetermined.	
· Flash point:	93 °C	
· Flammability (solid, gas):	Not applicable.	
· Ignition temperature:	190 °C	
· Decomposition temperature:	Not determined.	
· Auto-ignition temperature:	Product is not selfigniting.	
· Explosive properties:	Product does not present an explosion hazard.	
<ul> <li>Explosion limits: Lower: Upper:</li> </ul>	1.2 Vol % 12.2 Vol %	(0



Printing date 03.06.2020	Version number 302	Revision: 03.06.2020
Trade name: PU Foam Remover E-COLL		
· Oxidising properties	Not determined.	(Contd. of page 5)
Oxidialing properties	Not determined.	
· Vapour pressure:	Not determined.	
· Density at 20 °C:	1.57 g/cm³	
· Relative density	Not determined.	
· Vapour density	Not determined.	
· Evaporation rate	Not determined.	
· Solubility in / Miscibility with		
water:	Fully miscible.	
· Partition coefficient: n-octanol/water:	Not determined.	
· Viscosity:		
Dynamic:	Not determined.	
Kinematic:	Not determined.	
VOC (EC) %	39.00 %	
· 9.2 Other information	No further relevant information available.	

## **SECTION 10: Stability and reactivity**

- · 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- Thermal decomposition / conditions to be avoided: No decomposition if used according to specifications.
- · 10.3 Possibility of hazardous reactions Reacts with strong acids and oxidising agents.
- · 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known.

## **SECTION 11: Toxicological information**

#### 11.1 Information on toxicological effects

· Acute toxicity Based on available data, the classification criteria are not met.

	· LD/LC50 values relevant for classification:			
CAS: 141-43-5 2-aminoethanol				
	Oral	LD50	2,050 mg/kg (rat)	
	Dermal	LD50	1,000 mg/kg (rabbit)	
			(Contd. on page 7)	

- EU ---



Printing date 03.06.2020

Version number 302

Revision: 03.06.2020

Trade name: PU Foam Remover E-COLL

(Contd. of page 6)

- · Primary irritant effect:
- Skin corrosion/irritation Causes skin irritation.
- Serious eye damage/irritation Causes serious eye irritation.
- Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- Reproductive toxicity Based on available data, the classification criteria are not met.
- STOT-single exposure Based on available data, the classification criteria are not met.
- STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.

## **SECTION 12: Ecological information**

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- · 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Additional ecological information:
- · General notes:

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- · 12.5 Results of PBT and vPvB assessment
- · **PBT:** Not applicable.
- · vPvB: Not applicable.
- · 12.6 Other adverse effects No further relevant information available.

EU -



Printing date 03.06.2020

Version number 302

Revision: 03.06.2020

Trade name: PU Foam Remover E-COLL

(Contd. of page 7)

## **SECTION 13: Disposal considerations**

#### · 13.1 Waste treatment methods:

Containers can be recycled if completely empty; if not, dispose product/containers as dangerous waste. Observe local regulations.

<ul> <li>European w</li> </ul>	aste catalogue
--------------------------------	----------------

07 01 04\* other organic solvents, washing liquids and mother liquors

15 01 02 plastic packaging

15 01 10\* packaging containing residues of or contaminated by hazardous substances

· Recommended cleansing agents: Water, if necessary together with cleansing agents.

## **SECTION 14: Transport information**

· 14.1 UN-Number · ADR, ADN, IMDG, IATA	Void
<ul> <li>14.2 UN proper shipping name</li> <li>ADR</li> <li>ADN, IMDG, IATA</li> </ul>	UN- Void
· 14.3 Transport hazard class(es)	
· ADR · Class · Label · ADN/R Class:	- (-) - Void
· IMDG, IATA · Class · Label	Void -
<ul> <li>· 14.4 Packing group</li> <li>· ADR, IMDG, IATA</li> </ul>	Void
<ul> <li>• 14.5 Environmental hazards:</li> <li>• Marine pollutant:</li> </ul>	No
<ul> <li>14.6 Special precautions for user</li> </ul>	Not applicable.
<ul> <li>• 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</li> <li>• UN "Model Regulation":</li> </ul>	of Not applicable. Void

## **SECTION 15: Regulatory information**

· Directive 2012/18/EU

• Named dangerous substances - ANNEX I None of the ingredients is listed.

· REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3



Printing date 03.06.2020

# Safety data sheet according to 1907/2006/EC, Article 31

Version number 302

Revision: 03.06.2020

Trade name: PU Foam Remover E-COLL

(Contd. of page 8)

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

#### · Exposure scenario(s)

Exposure scenario(s) of ingredients (if present) are available on request at: sdb@ede.de

#### **SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

#### · Relevant phrases

H290 May be corrosive to metals. H302 Harmful if swallowed. H312 Harmful in contact with skin. H314 Causes severe skin burns and eye damage. H318 Causes serious eye damage. H332 Harmful if inhaled. H335 May cause respiratory irritation. H412 Harmful to aquatic life with long lasting effects. Abbreviations and acronyms: ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road) IMDG: International Maritime Code for Dangerous Goods IATA: International Air Transport Association GHS: Globally Harmonised System of Classification and Labelling of Chemicals EINECS: European Inventory of Existing Commercial Chemical Substances ELINCS: European List of Notified Chemical Substances CAS: Chemical Abstracts Service (division of the American Chemical Society) VOC: Volatile Organic Compounds (USA, EU) DNEL: Derived No-Effect Level (REACH) LC50: Lethal concentration, 50 percent LD50: Lethal dose, 50 percent PBT: Persistent, Bioaccumulative and Toxic vPvB: very Persistent and very Bioaccumulative Met. Corr.1: Corrosive to metals - Category 1 Acute Tox. 4: Acute toxicity - oral - Category 4 Skin Corr. 1B: Skin corrosion/irritation - Category 1B Skin Irrit. 2: Skin corrosion/irritation - Category 2 Eye Dam. 1: Serious eye damage/eye irritation – Category 1 Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) - Category 3

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard - Category 3

#### ·\* Data compared to the previous version altered.