

- Continuous short circuit protection
- I/O isolation: 1'060 VAC
- Operating temperature range
-40 to +85 °C without derating
- Input voltage ranges ($\pm 10\%$):
5, 12, 24 VDC
- High efficiency up to 82%
- SIP-7 package
- Unregulated outputs
- 3-year product warranty



The TBA 1E is an elementary 1 Watt DC/DC SIP converter series which is specifically designed to offer a low-cost solution with no concession on quality and lifetime. The new design improves on the industry standard features and offers an integrated continuous short circuit protection circuit, an operating temperature range from -40°C to 85°C without derating and I/O-isolations of either 1'060 VAC. It offers a broad application range in any space and cost critical application.

Models						
Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TBA 1-0511E	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	200 mA			79 %
TBA 1-0512E		12 VDC	84 mA			82 %
TBA 1-0513E		15 VDC	66 mA			82 %
TBA 1-0521E		+5 VDC	100 mA	-5 VDC	100 mA	79 %
TBA 1-0522E		+12 VDC	41 mA	-12 VDC	41 mA	82 %
TBA 1-0523E		+15 VDC	33 mA	-15 VDC	33 mA	82 %
TBA 1-1211E	10.8 - 13.2 VDC (12 VDC nom.)	5 VDC	200 mA			79 %
TBA 1-1212E		12 VDC	84 mA			80 %
TBA 1-1213E		15 VDC	66 mA			80 %
TBA 1-1221E		+5 VDC	100 mA	-5 VDC	100 mA	79 %
TBA 1-1222E		+12 VDC	41 mA	-12 VDC	41 mA	80 %
TBA 1-1223E		+15 VDC	33 mA	-15 VDC	33 mA	80 %
TBA 1-2411E	21.6 - 26.4 VDC (24 VDC nom.)	5 VDC	200 mA			79 %
TBA 1-2412E		12 VDC	84 mA			82 %
TBA 1-2413E		15 VDC	66 mA			82 %
TBA 1-2421E		+5 VDC	100 mA	-5 VDC	100 mA	79 %
TBA 1-2422E		+12 VDC	41 mA	-12 VDC	41 mA	82 %
TBA 1-2423E		+15 VDC	33 mA	-15 VDC	33 mA	82 %

Input Specifications

Input Current	- At no load	5 Vin models: 25 mA typ. 12 Vin models: 15 mA typ. 24 Vin models: 10 mA typ.
Surge Voltage		5 Vin models: 9 VDC max. (1 s max.) 12 Vin models: 18 VDC max. (1 s max.) 24 Vin models: 30 VDC max. (1 s max.)
Recommended Input Fuse		5 Vin models: 500 mA (slow blow) 12 Vin models: 200 mA (slow blow) 24 Vin models: 100 mA (slow blow)
Input Filter		Internal Capacitor (external capacitor recommended)

Output Specifications

Voltage Set Accuracy		±3% max. (at 60% for 5VDC models) ±3% max. (at 80% for other models)
Regulation	- Input Variation (Vmin - Vmax) - Load Variation - Cross Regulation (symmetrical load)	single output models: 1.5% max. (at 1% change of Vin) (see application note: www.tracopower.com/overview/tba1e) dual output models: 1% max.
Ripple and Noise	- 20 MHz Bandwidth	150 mVp-p max. 100 mVp-p typ.
Capacitive Load	- single output - dual output	5 Vout models: 2'200 µF max. 12 Vout models: 470 µF max. 15 Vout models: 470 µF max. 5 / -5 Vout models: 2'200 / 2'200 µF max. 12 / -12 Vout models: 470 / 470 µF max. 15 / -15 Vout models: 220 / 220 µF max.
Minimum Load		10 % of Iout max.
Temperature Coefficient		±0.02 %/K max.
Start-up Time		10 ms max.
Short Circuit Protection		Continuous, Automatic recovery

Safety Specifications

Safety Standards	- IT / Multimedia Equipment	Designed for EN 60950-1 (no certification)
------------------	-----------------------------	---

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +95°C +105°C max. -55°C to +125°C
Power Derating	- High Temperature	5 %/K above 85°C
Cooling System		Natural convection (20 LFM)
Switching Frequency		40 - 200 kHz (PWM)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'060 VAC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MOhm min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	10 pF max.
Reliability	- Calculated MTBF	2'000'000 h (MIL-HDBK-217F, ground benign)
Housing Material		Plastic (UL 94 V-0 rated)
Potting Material		Epoxy (UL 94 V-0 rated)
Pin Material		Tinned Copper
Connection Type		THD (Through-Hole Device)
Weight		2.3 g

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

Environmental Compliance - Reach
- RoHS


www.tracopower.com/info/reach-declaration.pdf
www.tracopower.com/info/rohs-declaration.pdf

Supporting Documents

[Overview Link](#) (for additional Documents)

www.tracopower.com/overview/tba1e

Outline Dimensions



Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	-Vout	-Vout
5	No pin	Common
6	+Vout	+Vout