


# AC/DC 35W Enclosed Switching Power Supply

TGR35-xx, TGR35-xx-C, TGR35-xx-Q Series



## FEATURES



- Universal 85 - 264VAC or 120 - 373VDC input voltage
- Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range: -30°C to +70°C
- Low standby power consumption, high efficiency
- High I/O isolation test voltage up to 4000VAC
- Low ripple & noise
- Output short circuit, over-current, over-voltage protection
- IEC/EN/UL62368, IEC/EN60335, GB4943, IEC/EN61558 safety approval
- Withstand 300VAC surge input for 5s
- Over-voltage class III (designed to meet EN61558)
- Operating altitude up to 5000m

TGR35-xx series is one of Tiger Power's enclosed AC-DC switching power supply. It features universal AC input and at the same time accepts DC input voltage, cost-effective, low no load power consumption, high efficiency and high reliability. These converters offer excellent EMC performance and meet IEC/EN61000-4, CISPR32/EN55032, IEC/UL/EN62368, IEC/EN60335, GB4943, IEC/EN61558 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home etc.

## Selection Guide

Certification	Part No.*	Output Power(W)	Nominal Output Voltage and Current (Vo/Io)	Output Voltage Adjustable Range(V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (μF)
UL, CE, CB, CCC	TGR35-5	35	5V/7A	4.5-5.5	83	8000
	TGR35-12	36	12V/3A	10.2-13.8	87	1500
	TGR35-15		15V/2.4A	13.5-18	89	1000
	TGR35-24		24V/1.5A	21.6-28.8	88	750

Note: \*Use suffix "C" for terminal with protective cover and suffix "Q" for conformal coating.

## Input Specifications

Item	Operating Conditions	Min.	Typ.	Max.	Unit
Input Voltage Range	AC input	85	--	264	VAC
	DC input	120	--	373	VDC
Input Voltage Frequency		47	--	63	Hz
Input Current	115VAC	--	--	0.8	A
	230VAC	--	--	0.6	
Inrush Current	115VAC	Cold start	30	--	
	230VAC		50	--	
leakage current	240VAC	<0.75mA			
Hot Plug		Unavailable			

## Output Specifications

Item	Operating Conditions	Min.	Typ.	Max.	Unit
Output Voltage Accuracy	Full load range	5V	±2	--	%
		12V/15V/24V	±1	--	
Line Regulation	Rated load	--	±0.5	--	
Load Regulation	0% - 100% load	5V	±1	--	
		12V/15V/24V	±0.5	--	
Ripple & Noise*	20MHz bandwidth (peak-to-peak value)	5V	80	--	mV
		12V/15V	120	--	
		24V	150	--	
Temperature Coefficient		--	±0.03	--	%/°C

# AC/DC 35W Enclosed Switching Power Supply

TGR35-xx, TGR35-xx-C, TGR35-xx-Q Series



Minimum Load		0	--	--	%
Stand-by Power Consumption		--	--	0.3	W
Hold-up Time	115VAC	8	--	--	ms
	230VAC	30	--	--	
Short Circuit Protection	Recovery time <5s after the short circuit disappear.	Hiccup, continuous, self-recovery			
Over-current Protection		110%-200% I <sub>o</sub> , self-recovery			
Over-voltage Protection	5V	≤ 6.3VDC (Output voltage clamp or hiccup)			
	12V	≤ 16.2VDC (Output voltage clamp or hiccup)			
	15V	≤ 21.75VDC (Output voltage clamp or hiccup)			
	24V	≤ 33.6VDC (Output voltage clamp or hiccup)			
Note: *The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information.					

## General Specifications

Item	Operating Conditions	Min.	Typ.	Max.	Unit		
Isolation	Input - $\oplus$	2000	--	--	VAC		
	Input-output	4000	--	--			
	Output - $\oplus$	1250	--	--			
Insulation Resistance	Input - $\oplus$	100	--	--	MΩ		
	Input - output	100	--	--			
	Output - $\oplus$	100	--	--			
Operating Temperature		-30	--	+70	°C		
Storage Temperature		-40	--	+85			
Storage Humidity	Non-condensing	--	--	95	%RH		
Operating Humidity	Non-condensing	20	--	90			
Switching Frequency		--	65	--	kHz		
Power Derating	Operating temperature derating	-30°C to -25°C	85VAC-100V AC	5	--	--	% / °C
		+50°C to +70°C		2	--	--	
	Input voltage derating	85VAC - 100VAC	1.33	--	--	% / VAC	
Safety Standard		IEC/EN/UL62368/IEC/EN60335/GB4943/IEC/EN61558					
Safety Certification		IEC/EN/UL62368/IEC/EN60335/GB4943/IEC/EN61558					
Safety Class		CLASS I					
MTBF	MIL-HDBK-217F@25°C	>300,000 h					

## Mechanical Specifications

Case Material	Metal (AL1100, SGCC)
Dimension	99.00 x 82.00 x 30.00 mm
Weight	170g (Typ.)
Cooling Method	Free air convection

## Electromagnetic Compatibility (EMC)



Emissions	CE	CISPR32/EN55032	CLASS B	
Emissions	RE	CISPR32/EN55032	CLASS B	
	Harmonic current	IEC/EN61000-3-2	CLASS A	
	ESD	IEC/EN 61000-4-2	Contact ±6KV / Air ±8KV	Perf. Criteria A
Immunity	RS	IEC/EN 61000-4-3	10V/m	perf. Criteria A
	EFT	IEC/EN 61000-4-4	±2KV	perf. Criteria A
	Surge	IEC/EN 61000-4-5	line to line ±2KV/line to ground ±4KV	perf. Criteria A
	CS	IEC/EN61000-4-6	10 Vr.m.s	perf. Criteria A
	Voltage dip, short interruption and voltage variation	IEC/EN61000-4-11	0%, 70%	perf. Criteria B

# AC/DC 35W Enclosed Switching Power Supply

TGR35-xx, TGR35-xx-C, TGR35-xx-Q Series



## Product Characteristic Curve




- Note: ① With an input voltage between 85 -100VAC and a DC input between 120-140VDC the output power must be derated as per the temperature derating curves;
- ② This product is suitable for applications using natural air cooling; for applications in closed environment please consult Tiger.



## Dimensions and Recommended Layout

TGR35-xx、TGR35-xx-Q Series




# AC/DC 35W Enclosed Switching Power Supply

TGR35-xx, TGR35-xx-C, TGR35-xx-Q Series



## TGR35-xx-C Series



- Note:**
- For additional information on Product Packaging please refer to [www.TigerPowerSupplies.com](http://www.TigerPowerSupplies.com);
  - Unless otherwise specified, parameters in this datasheet were measured under the conditions of  $T_a=25^{\circ}\text{C}$ , humidity<75%RH with nominal input voltage and rated output load;
  - The room temperature derating of  $5^{\circ}\text{C}/1000\text{m}$  is needed for operating altitude greater than 2000m;
  - All index testing methods in this datasheet are based on our company corporate standards;
  - In order to improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability;
  - We can provide product customization service, please contact our technicians directly for specific information;
  - Products are related to laws and regulations: see "Features" and "EMC";
  - The out case needs to be connected to the earth of system when the terminal equipment in operating;
  - Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.