


AC2403



AS-Interface CompactLine module

CompactM12 2 AI C V4A



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	250
Reverse polarity protection		yes

Inputs / outputs

Number of inputs and outputs	Number of analogue inputs: 2
------------------------------	------------------------------

Inputs

Number of analogue inputs	2; (Anschluss von 2- und 4-Draht-Sensoren)
Analogue input (current) [mA]	4...20

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67; (when flat cables are used E7400x / E7401x)

Tests / approvals

EMC	EN 50295
MTTF [years]	167

AC2403

AS-Interface CompactLine module

CompactM12 2 AI C V4A



AS-i classification		
AS-i version		2.11 + 3.0
AS-i addressing		IR addressing possible
Extended addressing mode possible		no
AS-i profile		S-7.3.D
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	3.D
AS-i certificate		99201
Mechanical data		
Weight	[g]	277
Type of mounting		AS-i flat cables directly connectable
Materials		PA; socket: stainless steel (1.4404 / 316L); threaded inserts in the lower part: stainless steel (1.4404 / 316L); screws in the lower part: stainless steel (1.4578 / 316Cu); piercing contacts: CuSn6 nickel-plated and tin-plated
Displays / operating elements		
Display	operation	LED, green Voltage AS-i
	errors	LED, red
	function	LED, yellow channels AI1, AI2
Accessories		
Accessories (optional)		Protective cap: M12, E73004
		Stainless steel sleeve, for installation in case of high mechanical stress , E70402
Remarks		
Remarks		The module is exclusively supplied via the yellow AS-i cable.
		When connecting a 2-wire or 3-wire sensor without own supply there has to be an external link between pin 3 and pin 4.
		The inputs (pins 2 and 4) are electrically separated and have no connection to AS-i.
Pack quantity		1 pcs.
Electrical connection		
1		Sensor supply +24V
2		analogue input AI +
3		Sensor supply 0V / analogue input AI-
4		analogue input AI -
5		functional earth
Connector: M12		

