

RECHARGEABLE LED INSPECTION LIGHT 1000 LM

Référence	MDM	EAN
887712	13276916	3660338410949

Description

Li-Ion rechargeable LED inspection light.
 Lighting Power 1000 Lumens max.
 Strong magnetic base with 180° adjustable handle.
 2 useful hooks on the light's back.
 3 brightness levels + 1 "torch" mode



180° Adjustable Handle



2x Hook on Back



Technical characteristics

LED Type	Super bright 1x SMD + 1x COB LED
Lighting Power top light	170 lumens
Lighting Power main light	250/500/1000 lumens
CRI	80 CRI+
CCT	6500K
Battery	3,7V 3350 mAh Li-ion Battery
Running time	Top light : 7h / Main light : 7h/3h/1,5h
Charging time	5h

Standards and certifications

IP65 IK09

Packaging

- 1 unit, delivered with USB-C cable