

Spacer sleeve for MK with flat tangs (DIN 6383)

in accordance with ISO 7388-1

ATORN[®]

Application

For holding tools with Morse taper shank and flat tangs in accordance with DIN 228-1 form B.

Version

- Alloyed case-hardened steel with tensile strength at the core of at least 950 N/mm²
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm, bronzed
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- Max. concentricity < 0.005 mm



Art. no.	23163 061
Mount, on tool side	MK 2
Projecting length	50 mm
Outer diameter	32 mm
Tool holding device	SK 30

EAN-Code

40502937 15040