

**WIL-STANDARD-0.3-SCREW-SW-WHI**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The WIL-LED lights Family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

**General ordering data**

Type	WIL-STANDARD-0.3-SCREW-SW-WHI
Order No.	<a href="#">2436210000</a>
GTIN (EAN)	4050118448306
Qty.	1 Stück

## WIL-STANDARD-0.3-SCREW-SW-WHI

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	240 mm	Width (inches)	9.449 inch
Height	8 mm	Height (inches)	0.315 inch
Depth	40 mm	Depth (inches)	1.575 inch
Net weight	200 g		

### Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-20 °C
Operating temperature	-20 - 60°C		

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	0.3 m		

### Connection data

Version	pin, straight	Coding	A
Connection thread	M12	Tightening torque	0.8 Nm
Wiring	Pin 4 (Strand: black) control white LED, Pin 3 (Strand: blue)		

### Electric data

Rated voltage (text)	24 V DC	Rated current	0,42 A
Power	8,5 W	Dimmable	Yes

### General technical data

Number of LEDs	42	Light colour (CCT)	6500K, White
Luminosity	3,470 cd	Light current	711 lm
Emitting angle	40 °	Illumination level	245 lux
Operating life	60.000 h	Type of mounting	Screw mounting
Drill hole spacing	225 mm	Impact resistance	IK05
Protection degree	IP67		

### Material data

Housing main material	hard anodised aluminium	Encapsulation compound	PUR V0
Threaded ring material	PA	Material of end caps	Diecast zinc, nickel-plated

### Standards

Certificate no. (cULus)	E354496
-------------------------	---------

### Classifications

ETIM 6.0	EC001959	ETIM 7.0	EC001959
eClass 9.0	27-11-06-40	eClass 9.1	27-11-06-40
eClass 10.0	27-11-06-40		

Erstellungs-Datum January 27, 2020 12:30:37 PM CET

**WIL-STANDARD-0.3-SCREW-SW-WHI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten****Approvals**

Approvals



ROHS

Conform

**Downloads**


Brochure/Catalogue	<a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN</a>
Engineering Data	<a href="#">STEP</a>

**WIL-STANDARD-0.3-SCREW-SW-WHI**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Zeichnungen**

**Dimensioned drawing**



L = 240mm, L1 = 225mm

Housing Length L	Drill hole spacing L1
145 mm	130 mm
240 mm	225 mm
350 mm	335 mm
450 mm	435 mm
555 mm	540 mm
655 mm	640 mm
765 mm	750 mm
860 mm	845 mm

L = 240mm, L1 = 225mm