


## Switched-Mode Power Supply, 1-Phase

EPSITRON® COMPACT Power



- Primary switch mode power supply unit
- Prepared for class II equipment
- Natural convection cooling when horizontally mounted
- Stage profile, ideal for distribution boards or distribution boxes
- Parallel operation, series connection possible
- Electrically isolated output voltage (SELV) acc. to EN 60950-1/UL 60950

Description	Item No.	Pack. Unit
Switched-Mode Power Supply, 24 VDC / 1.3A	787-1002	1

Technical Data	
<b>Input:</b>	
Nominal input voltage $V_i$ nom	100 ... 240 VAC
Input voltage range	85 ... 264 VAC; 120 ... 373 VDC
Input voltage derating	< 100 VAC: $I_a$ max. 1 A
Frequency	44 ... 66 Hz; 0Hz
Input current $I_i$	0.7 A at 110 VAC / 0.5 A at 230 VAC
Discharge current	1 mA typ.
Inrush current	< 30 A, NTC
Mains failure hold-up time	> 10 ms at 110 VAC / > 80 ms at 230 VAC
<b>Output:</b>	
Nominal output voltage $V_o$ nom	24 VDC (SELV)
Output voltage range	22.8 ... 26.4 VDC adjustable
Output current $I_o$	1.3 A at 24 VDC max. 0.9 A in any mounting position
Factory preset	24 VDC
Adjustment accuracy	2%
Residual ripple	< 100 mV (peak-to-peak) at 20 MHz
Current limitation	$1.1 \times I_o$ typ.
Overload behavior	Constant current
Operational indication	LED green ( $V_o$ )
<b>Efficiency / power losses:</b>	
Efficiency	82 % typ.
Power loss $P_V$	2.6 W (230 VAC/no load), 7.0 W (230 VAC/rated load)
Max. power loss $P_V$	7.3 W typ. (100 VAC / 24 VDC, 1.3 A)
<b>Fuse protection:</b>	
Internal fuse	T 2 A / 250 V
External fuse	Circuit breakers 10 A, 16 A, characteristic: B or C An external DC fuse is required for the DC input voltage

Technical Data	
<b>Environmental requirements:</b>	
Ambient operating temperature	-25 °C ... +60 °C (UL: -25 °C ... +55 °C); Device start at -40 °C (type-tested)
Storage temperature	-25 °C ... +80 °C
Rel. humidity	5 % ... 96 % (no condensation)
Derating	-3 % / K (> 45 °C)
Degree of pollution	2 (acc. to EN 50178)
Climatic category	3K3 (acc. to EN 60721)
<b>Safety and protection:</b>	
Enclosure	Plastic, light gray, Flammability class V0 acc. to UL94
Test voltage pri. - sec.	4.2 kV DC
Protection class	Prepared for class II equipment
Degree of protection	IP20 (acc. to EN 60529)
Overvoltage protection	< 40 VDC (in the event of a fault)
Short circuit protection	yes
No-load proof	yes
Feedback voltage	max. 30 VDC
Parallel operation	yes
Series connection	yes
MTBF	500000 h
<b>Connection and type of mounting:</b>	
Wire connection	Input/Output: WAGO 740 Series
Cross sections	Input/Output: 0.08 ... 2.5 mm <sup>2</sup> / AWG 28 ... 12
Strip lengths	Input/Output: 6 ... 7 mm / 0.24 ... 0.28 in
Type of mounting	DIN-rail mount (EN 60715)
<b>Dimensions and weight:</b>	
Dimensions (mm) W x H x L	54 x 89 x 59 Length: 55 mm, from upper-edge of DIN 35 rail
Weight	180 g
<b>Standards and approvals:</b>	
Standards/Specifications	EN 60950, EN 61204-3, UL 60950, UL 508, GL