

### Einsatzempfehlung

Material	Stahl N/mm <sup>2</sup>				Rostfreie Stähle		Guss		NE-Metalle			Superleg.		Stahl gehärtet	
Zugfestigkeit	<500	<800	<1200 (<HRC38)	<1600 (<HRC48)	<800	<1200	GG	GGG	Al Knetleg.	Al Si<10%	Cu, Ms	Ti/Ni/Co <900	900-1500	HRC 48-57	HRC 58-63
40 00 867 363 - Vc (m/min)	23	12	12	10	12	10	20		28	24	16				
Kühlung	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl		Emulsion/Öl	Emulsion/Öl	Emulsion/Öl				