

P/N: TA70

Revision

29570

Last modified

2015-10-13 15:56 UTC+1

Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@fir.com with any questions.

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>



Part number	TA70
Part description	CAT IV Insulated Alligator Probes
<ul style="list-style-type: none"> • Works with FLIR TA80 test probes. • Complies with latest UL CAT IV/CAT III—1000 V. • Slide-on connection with finger guards. • 2 year warranty. 	

Specifications	
Maximum capacity	10 A
Operating temperature	-10 to 50°C (14 to 122°F)
Relative humidity	Maximum relative humidity 80% for temperature up to 31°C (88°F) decreasing linearly to 50% relative humidity at 50°C (122°F)
Storage temperature	-20 to 60°C (-4 to 140°F), <80% relative humidity
Altitude	Operating below 2000 m (6562')

Meter data	
Suitable main unit	FLIR TA80 test leads
Warranty	2 years

Certifications	
Certifications	IEC/EN 61010-031:2008 and UL 61010-031:2010 to 600 V CAT IV and 1000 V CAT III

Meter physical data	
Weight	0.02 kg
Dimensions (H x W x L)	7.94 cm x 4.13 cm x 1.91 cm
Material	Nickel-plated steel, TPR and polypropylene
Color	Black and red

Shipping information	
Packaging type	Color box
Packaging contents	Manual, TA70 alligator clips
Packaging weight	0.05 kg