

Indexable milling insert WPR-DN

For steel and cemented carbide die-sinking cutter no. 16120 and 16121

KIENINGER

Execution:

- Grades LCP30M and LCPK 10M with Nanomold Gold coating

Delivery:

Box quantity: up to Ø 20 mm = 10 pc., Ø 25 and 32 mm = 5 pc, exception: ref. no. 760-774

Art. no.	16128 764
Brand	KIENINGER
Manufacturer Part Number	9074409
ISO standard	WPR-DN
Diameter of indexable insert	16 mm
Thickness of indexable insert	3 mm
Edge radius	8 mm
Indexable insert no.	3
Surface	Coated
Coating	Diamond
Carbide type	LCN10M/K10
Material to be processed	Non-ferrous metal, Graphite
Gross Weight	0.012 kg
Product Group	1K1

