

## KLH blade holder, left, with clamping element

For holding cutting inserts, no. 17710-17717



### Application:

For cutting off and plunging with cutting inserts with no. 17710-17717.

### Execution:

- Precision-machined steel holder, burnished and hardened

### Advantage:

- High-quality, hard-wearing steel holder with high-strength clamping element
- Precision-machined plate seat



<b>Art. no.</b>	<b>17704 313</b>
<b>Brand</b>	KELL-LOCK
<b>Manufacturer Part Number</b>	KLH/L 313
<b>Width of cutting edge</b>	3.1 mm
<b>Shaft height</b>	20 mm
<b>Shank width</b>	20 mm
<b>Programming size</b>	12 mm
<b>Programming size 2</b>	36 mm
<b>Length</b>	130 mm
<b>Immersion depth</b>	90 mm
<b>Max. diameter</b>	55 mm
<b>Tool design</b>	Left
<b>Gross Weight</b>	0.385 kg
<b>Product Group</b>	181