



Figure similar

COMMUTATING CHOKE FOR CONVERTER;  
 PHASES:1; UN1(V):400; ITHMAX 1(A) / F1(HZ):10 /50;  
 I LN (A):9; UK(%):4; LN(MH):4,84; TA/ISOKL:40 /B;  
 IP00; TYPE OF TERMINALS:SCREW/TAB  
 CONNECTION; EN 61558-2-20 >CHOKE<

### General technical data:

<b>Product designation</b>		Kommut.-Drossel f. Stromrichter
<b>product brand name</b>		SIDAC
<b>Phase number</b>		1
<b>Type of voltage</b>		AC
<b>Operating voltage Rated value</b>	V	400
<b>Operating frequency Rated value</b>	Hz	50
<b>Current</b>		
• with AC		
— Rated value	A	9
— maximum	A	10
• for DC Rated value	A	12.2
<b>Inductivity Rated value</b>	H	0.0048
<b>Relative inductive drop in voltage on the measurement level current, voltage and frequency</b>	%	4
<b>Active power loss of the coil</b>	W	10.7
<b>Active power loss of the iron core</b>	W	14.4

### Mechanical data:

<b>Type of electrical connection for main current circuit</b>		screw-type terminals / tab terminals
<b>Width</b>	m	0.085
<b>Height</b>	m	0.103
<b>Depth</b>	m	0.108

### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		B
<b>Ambient temperature Rated value</b>	°C	40

Protection class IP

IP00

Certificates/ approvals:

Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EM49117CB00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4EM49117CB00>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4EM49117CB00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EM49117CB00&lang=en)

last modified:

16.03.2015