


# PA3224



## Pressure transmitter with ceramic measuring cell

PA-010-RBN14-A-ZVG/US/ IV



### Product characteristics

Output signal	analogue signal		
Measuring range	0...10 bar	0...145 psi	0...1000 kPa
Process connection	threaded connection 1/4 NPT internal thread		

### Application

Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	75...90; (on request: -40...90 °C)		
Pressure rating	75 bar	1088 psi	7.5 MPa
Min. bursting pressure	150 bar	2175 psi	15 MPa
Type of pressure	relative pressure		

### Electrical data

Operating voltage [V]	9.6...32 DC		
Min. insulation resistance [ $M\Omega$ ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		

### Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

## Pressure transmitter with ceramic measuring cell

PA-010-RBN14-A-ZVG/US/ /V

Outputs			
Total number of outputs		1	
Output signal		analogue signal	
Number of analogue outputs		1	
Analogue current output [mA]		4...20	
Max. load [Ω]		720; ( $U_b = 24 \text{ V}$ ; $(U_b - 9,6 \text{ V}) / 20 \text{ mA}$ )	
Overload protection		yes	
Measuring/setting range			
Measuring range	0...10 bar	0...145 psi	0...1000 kPa
			0...1 MPa
Accuracy / deviations			
Repeatability [% of the span]		< 0,1; (with temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]		< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)	
Long-term stability [% of the span]		< ± 0,05; (per 6 months)	
Temperature coefficient zero point [% of the span / 10 K]		0,1; (0...80 °C)	
Temperature coefficient span [% of the span / 10 K]		0,2; (0...80 °C)	
Response times			
Step response time analogue output [ms]		3	
Operating conditions			
Ambient temperature [°C]		-25...80	
Storage temperature [°C]		-40...100	
Protection		IP 65	
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	30 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
	radiation of interference	according to the automotive directive 2004/104/EC	
	CISPR 25		
	immunity	according to the automotive directive 2004/104/EC	
Shock resistance	ISO 11452-2 HF radiated	100 V/m	
	ISO 7637-2 pulse	severity level 4	
	DIN EN 60068-2-27	50 g (11 ms)	
	DIN EN 61373	category 3	
	DIN EN 60068-2-6	20 g (10...2000 Hz)	
Vibration resistance	DIN EN 61373	category 2	
	MTTF [years]	506	
	Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
	Railway applications	DIN EN 50155 / IEC 60571	Klasse T3, C1, S1

# PA3224



## Pressure transmitter with ceramic measuring cell

PA-010-RBN14-A-ZVG/US/ IV

### Mechanical data

Weight	[g]	224
Materials		stainless steel (1.4404 / 316L); FKM; PA; EPDM/X
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; FKM
Min. pressure cycles		100 million
Process connection		threaded connection 1/4 NPT internal thread
Restrictor element integrated		no (can be retrofitted)

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; Contacts: gold-plated



### Connection

