Reflex Sensor

with Background Suppression

HM24PCT2

Part Number




- Electronic background suppression
- Red light
- Teach-in, external teach-in

Technical Data

rechnical Data						
Optical Data						
Range	150 mm					
Adjustable Range	40150 mm					
Switching Hysteresis	< 5 %					
Light Source	Red Light					
Service Life (T = +25 °C)	100000 h					
Max. Ambient Light	10000 Lux					
Light Spot Diameter	see Table 1					
Electrical Data						
Supply Voltage	1030 V DC					
Current Consumption (Ub = 24 V)	< 30 mA					
Switching Frequency	900 Hz					
Response Time	555 μs					
On-/Off-Delay (RS-232)	01 s					
Temperature Drift	< 5 %					
Temperature Range	-2560 °C					
Switching Output Voltage Drop	< 2,5 V					
PNP Switching Output/Switching Current	200 mA					
Short Circuit Protection	yes					
Reverse Polarity Protection	yes					
Overload Protection	yes					
Lockable	yes					
Teach Mode	HT, VT					
Protection Class	III					
Mechanical Data						
Setting Method	Teach-In					
Housing Material	Plastic					
Full Encapsulation	yes					
Degree of Protection	IP67					
Connection	M12 × 1; 4-pin					
PNP NO/NC switchable	•					
RS-232 with Adapterbox						
Connection Diagram No.	152					
Control Panel No.	M3					
Suitable Connection Equipment No.	2					
Suitable Mounting Technology No.	360					


These sensors detect distance by measuring angles. They are particularly good at recognizing objects in front of any background. The color, shape and surface characteristics of the object have practically no influence on sensor switching performance.




Complementary Products

Adapterbox A232	
PNP-NPN Converter BG2V1P-N-2M	
Protective Housing ZSV-0x-01	
Set Protective Housing ZSM-NN-02	
Software	






Ctrl. Panel



06 = Teach Button 30 = Switching Status/Contamination Warning



_egen	id		PT	Platinum measuring resistor	ENARS422	Encoder A/Ā (TTL)
+	Supply Voltage +		nc	not connected	ENBRS422	Encoder B/B (TTL)
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B
Α	Switching Output (NO)	W	Trigger Input	Amin	Digital output MIN
A	Switching Output ((NC)	W -	Ground for the Trigger Input	Амах	Digital output MAX
V	Contamination/Error Output (NO)	0	Analog Output	Аок	Digital output OK
V	Contamination/Error Output ((NC)	0-	Ground for the Analog Output	SY In	Synchronization In
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT
Т	Teach Input		Awv	Valve Output	OLT	Brightness output
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance
S	Shielding		b	Valve Control Output 0 V	rsv	reserved
RxD	Interface Receive Path		SY	Synchronization	Wire Co	lors according to DIN IEC 757
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black
RDY	Ready		E+	Receiver-Line	BN	Brown
GND	Ground		S+	Emitter-Line	RD	Red
CL	Clock		±	Grounding	OG	Orange
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow
②	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey
Signal			Mag	Magnet activation	WH	White
BI_D+/-	Ethernet Gigabit bidirect. data I	line (A-D)	RES	Input confirmation		Pink
	Encoder 0-pulse 0-0 (TTL)	, ,	EDM	Contactor Monitoring	GNYE	Green/Yellow

Table 1

Detection Range	60 mm	100 mm	150 mm
Light Spot Diamete	4 mm	5 mm	10 mm

Switching Distance Deviation

Typical characteristic curve based on white, 90 % remission

