

### Inductors for power circuits

Size  $12.4 \times 13.1 \times 11.5$  (mm)

Series/Type: PCM120T

Date: April 2021

<sup>©</sup> TDK Electronics AG 2021. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



#### Inductors for power circuits

Size 12.4 x 13.1 x 11.5 (mm)

**PCM120T** 

<u>SMD</u>

Rated inductance 0.4 ... 10 µH Rated current 12.0 ... 79.8 A

#### Construction

- Metal rod core
- Magnetically shielded
- Winding: enamel copper wire
- Flat wire connection



- Current-handling capability up to 80 A, soft saturation
- AOI (solder point inspection) suitable
- Lead frame provides good coplanarity and solderability
- High mechanical robustness
- High magnetic shield construction featuring low EMI
- Temperature range up to +165 °C
- Suitable for lead-free reflow soldering as referenced in JEDEC J-STD 020D
- Qualification to AEC-Q200
- RoHS-compatible

#### **Applications**

- Primary DC/DC converters (withstands ISO7637 pulses)
- Automotive electronics (PMIC power management integrated circuits,
   ECM engine control module, transmission control, power steering control)
- Power supply in servers
- Power supplies in 5G base stations

#### **Terminals**

- Base material Cu
- terminal finish Sn (lead-free)
- Electro-plated

#### Marking

- Marking on component:
   Series name, L value (μH, coded), manufacturing date (YWWD)
- Minimum data on reel: Manufacturer, ordering code, L value, quantity, date of packing

#### Delivery mode and packing unit

- 32-mm blister tape, wound on 330-mm Ø reel
- Packing unit: 250 pcs./reel





**PCM120T** 


#### Size 12.4 x 13.1 x 11.5 (mm)

#### **SMD**

#### Dimensional drawing and layout recommendation








1) Soldering area

IND1725-6-E

Dimensions in mm

#### **Taping and packing**





1 1 4	•			100
Inductors	tor	nower	circi	IIIte
IIIGUGLOIS				

PCM120T

Size 12.4 x 13.1 x 11.5 (mm)

#### **SMD**

#### Technical data and measuring conditions

(Measured at room temperature unless otherwise noted)

Rated inductance L <sub>R</sub>	Measured with LCR meter Agilent 4284A at frequency f <sub>L</sub> , 0.1 V			
Operating temperature range	−55 °C +165 °C			
Thermal current I <sub>temp</sub>	Max. permissible DC with temperature increase of $\leq$ 40 K (to IEC 62024-2)			
Saturation current I <sub>sat</sub>	Max. permissible DC with inductance decrease $\Delta L/L_0$ of 30% of its nominal value			
DC resistance R <sub>DC</sub>	Measured with Burster Resistomat 2329			
Solderability (lead-free)	Dip and look method Sn95.5Ag3.8Cu0.7: $+(245 \pm 5)$ °C, $(5 \pm 0.3)$ s Wetting of soldering area $\geq 90\%$ (based on IEC 60068-2-58)			
Resistance to soldering heat	as referenced in JEDEC J-STD 020D			
Climatic category	55/165/56 (to IEC 60068-1)			
Storage conditions	onditions			
Weight	Approx. 6 g			

#### **Characteristics and ordering codes**


L <sub>R</sub>	Tol.	Meas.	R <sub>DC</sub>	Rated current		rent	Internal code	Ordering code
		freq.		I <sub>sat,typ</sub>	I <sub>sat,min</sub>	I <sub>temp,typ</sub>		
μΗ		kHz	mΩ	Α	Α	Α		
0.40	±30%	100	0.72 ±30%	79.80	67.8	50.0	B82482M1401N000	PCM120T-R40N-D
0.50	±30%	100	0.72 ±30%	58.7	49.9	50.0	B82482M1501N000	PCM120T-R50N-D
0.68	±30%	100	0.83 ±30%	49.5	40.6	46.6	B82482M1681N000	PCM120T-R68N-D
0.82	±30%	100	1.06 ±30%	49.3	40.5	41.2	B82482M1821N000	PCM120T-R82N-D
1.0	±30%	100	1.06 ±30%	39.5	33.6	41.2	B82482M1102N000	PCM120T-1R0N-D
1.2	±30%	100	1.45 ±30%	38.7	32.9	35.2	B82482M1122N000	PCM120T-1R2N-D
1.5	±20%	100	1.45 ±20%	32.2	27.4	35.2	B82482M1152N000	PCM120T-1R5N-D
2.2	±20%	100	2.45 ±20%	24.8	20.5	27.1	B82482M1222M000	PCM120T-2R2M-D
2.7	±20%	100	3.12 ±20%	26.3	20.4	24.4	B82482M1272M000	PCM120T-2R7M-D
3.3	±20%	100	3.12 ±20%	20.9	16.7	24.4	B82482M1332M000	PCM120T-3R3M-D
4.7	±20%	100	4.30 ±20%	17.0	14.9	20.6	B82482M1472M000	PCM120T-4R7M-D
6.8	±20%	100	6.50 ±20%	15.1	13.2	16.6	B82482M1682M000	PCM120T-6R8M-D
8.2	±20%	100	9.00 ±20%	15.0	11.5	14.1	B82482M1822M000	PCM120T-8R2M-D
10.0	±20%	100	9.00 ±20%	12.0	10.2	14.1	B82482M1103M000	PCM120T-100M-D




#### **SMD**

# Inductance L versus DC superposition I<sub>DC</sub> measured with LCR meter Agilent 4284A and Agilent 42842, typical values at +20 °C


#### PCM120T-R40N-D




#### PCM120T-R50N-D



#### PCM120T-R68N-D




#### PCM120T-R82N-D






#### PCM120T-1R0N-D




#### **SMD**


#### PCM120T-1R2N-D



#### **PCM120T-1R5N-D**




#### PCM120T-2R2M-D







#### PCM120T-2R7M-D




#### PCM120T-3R3M-D



#### PCM120T-4R7M-D




#### PCM120T-6R8M-D







#### PCM120T-8R2M-D



#### PCM120T-100M-D



## Current derating $I_{op}/I_R$ versus ambient temperature $T_A$





#### **Cautions and warnings**

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
  - Particular attention should be paid to the derating curves given there.
  - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.

  Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.
- The following points must be observed if the components are potted in customer applications:
  - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
  - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
  - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.

#### Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



#### Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
  - We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).

10



#### Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.

Release 2018-06