

Yodalarm[®] YA80 Super

Multi-Purpose Audible Signalling Device designed for use in Fire, Industrial & Marine applications with **High Ambient Background Noise**

PRODUCT FEATURES

- Max sound output 120 dB(A) @ 1m
- IP66 rated as standard
- 32 selectable tones meeting international regulations
- Flame retardant ABS enclosure
- Stainless steel fixings
- 2 stage alarm
- Independently selectable second stage

Product Approvals

Marine Equipment Directive MED Regulations EN 54-3:2014 incl. A1:2019 IEC 60092-504:2016 IEC 60533:2015 Module B (BSI/MED/3.53/756093) Module D (BSI/MED/PC/756095)

Merchant Shipping (Marine Equipment) Regulations EN 54-3:2014 incl. A1:2019, IEC 60092-504:2016, IEC 60533:2015 Module B (BSI/UK/3.53/738807) Module D (BSI/UK/PC/738808)

EN 54-3 : 2001 + A1:2002 + A2:2006 Type B 2797-CPR-713892



8



UK BS EN 54-3 : 2001 + A1:2002 + A2:2006 Type B 0086-CPR-774029



BS EN 54-3 : 2001 + A1:2002 + A2:2006 Type B KM 713890

Compliant



UK +44 (0) 121 446 5322 FR +33 (0)1 70 72 12 71 🖄 uksales@moflash.co.uk

(6

www.moflash.com

exportsales@moflash.co.uk

TECHNICAL DATA

Electrical Data		Acoustic Data			
Operating Voltage	Current Draw	Maximum Volume Output	120dB (A)		
24vDC	500mA at Tone 1	2 Stage Alarm with Independently Sel	ectable tones via DIL Switch		
48vDC	300mA				
115vAC ~	200mA	Mounting / Installa	ation		
230vAC ~	130mA	Devices should be mounted to a suitable flat wall or			
Ambient Conditions Operating Temperatures		bulkhead avoiding any undue vibration and using the two lugs projecting from the case. The lugs are bored 10mm on 250mm centres. The minimum length of fixing screw required is 30mm. To maintain the IP rating of the enclosure,			
					Standard General
EN54 Pt:3 Fire	-25 °C to +55 °C	gland (included). Max cable termination	nd (included). Max cable termination 2.5mm ² .		
Storage Temperature	-40 °C to +70 °C				
Max. Relative Humidity	93% ± 3 at 40 °C		rity on DC Systems		
		 For 3 wire 2 stage alarm system, For 2 wire 2 stage alarm system, 	monitor via reverse polarity. monitor via threshold, (applied voltage<1v)		
Mechanic		an end-of-line (E.O.L) resistor is required for line monitoring and should have			
Enclosure Material	ABS FR UL94 5VB	a minimum resistance of 3k3 Oh type.	ms and 0.5 Watts, wire-wound or metal film		
External Fixings	Stainless Steel				
Degree of Protection	IP66 (IEC60529)				
		Multi-Stage Alarm			
The units are supplied wit details) across all voltage		n with Independently Selectable tones (s	see tone table on the installation sheet for		
	options as standard.				
		Dimensional Drawing			
We reserve the right to ma	ake alterations to the te	-	ns and products available without notice. The		
0	nsidered binding.				
illustrations cannot be co					
All Dimensions in mm [inc	ches] - Subject to alterat	ions			
	ches] - Subject to alterat	ions			
	ches] - Subject to alterat	ions Ø 10 [ø 0,39]		
	ches] - Subject to alterat		9]		
		ø 10 [ø 0,39			
		ø 10 [ø 0,39			
		ø 10 [ø 0,39			
	ches] - Subject to alterat	ø 10 [ø 0,39	219 [- 8,62]		
		ø 10 [ø 0,39			
		ø 10 [ø 0,39			
		ø 10 [ø 0,39	219 [

Issue

YA80 SUPER SIGNALLING DEVICES

SELECTION .

-	Version	Enclosure Colour	Rated Operational Voltage	Order number	Art. No.	Weight (kg)
	YA80 Super Sounder (RF) BS EN 54 Pt:3 UKCA, CE, EU MED & UK MER	24vDC	YA80/D/RF/SU/WR	204404	2.9	
		48vDC	YA80/F/RF/SU/WR	212660	2.9	
			115vAC ~	YA80/L/RF/SU/WR	204420	3.28
			230vAC ~	YA80/N/RF/SU/WR	204434	3.28