

## Drawer cabinet system 550 S with 2 SOFT-CLOSE drawers and 1 door

Depth 550 mm, width 722 mm

### Application:

Particularly suitable for careful storage of delicate, sensitive tools and parts in drawers.

### Execution:

- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Perforated steel sheet base (25 mm hole spacing) for fastening and fixing components
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- With door height 740 mm

### Advantage:

- The damping system brakes the drawer while closing; it closes the drawer smoothly and soundlessly by means of the self-closing mechanism
- Impact load on tools and parts stored in the drawer is reduced to a minimum due to the smooth-closing drawers
- High quality - made in Germany

FH mm	KH mm
90	70
120	100
740	



<b>Art. no.</b>	<b>50295 782</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50295782
<b>Number of drawers</b>	2 PCS
<b>With doors</b>	Yes
<b>Height</b>	1036 mm
<b>Width</b>	722 mm
<b>Depth</b>	550 mm
<b>Height x width x depth</b>	1036 x 722 x 550 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	600 x 450 mm
<b>Drawer with slots</b>	Yes
<b>Perforated drawer base</b>	Yes
<b>Load-carrying capacity per drawer</b>	100 kg
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>Pullout type</b>	Full extension
<b>With SOFT-CLOSE closing function</b>	Yes
<b>With single pull-out safety brake</b>	Yes
<b>Central locking</b>	Yes
<b>Material of cover panel</b>	Wood, plastic-coated
<b>Cabinet colour</b>	Optional
<b>Colour of front</b>	Optional
<b>Surface</b>	Powder-coated
<b>Model</b>	SK5 32/2
<b>Overall surface</b>	0.54 m <sup>2</sup>
<b>Lock type</b>	DOM® locking system
<b>Material</b>	Sheet steel
<b>Gross Weight</b>	97.000 kg
<b>Product Group</b>	5BB

### EAN

4053625049769