

Double-ended bench grinder DS 150 M

metabo®

Application:

Robust and compact machine for sharpening, sanding and deburring tasks

Version:

- Low-noise, low-vibration, maintenance-free induction motor
- Motor for single-phase alternating current
- Workpiece rests adjustable without tools
- Large spark protection screens to protect eyes
- Vibration-damping rubber feet for secure position



Art. no.	70574 011
Model	DS 150 M
Manufacturer Article Number	604150000
Power input	370 W
Power output	260 W
Disc diameter x disc thickness	150 x 20 mm
Disc hole diameter	20 mm
Weight	8.7 kg
Included in delivery	Synthetic corundum sanding discs 36 P and 60 N, spark protection screens, workpiece support

EAN-Code

406179222596 1

