

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0050291900](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK High Pressure Crimp Terminal 7879, 24-30 AWG, Reel Tin (Sn)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-2759-002-001 \(PDF\)](#)

General

| | |
|-------------------------|---|
| Product Family | Crimp Terminals |
| Series | 7879 |
| Application | Signal, Wire-to-Board |
| Crimp Quality Equipment | Yes |
| Overview | KK® Interconnect System - Molex |
| Packaging Alternative | 46999-0101 (Loose) |
| Product Name | KK High Pressure |
| UPC | 822348742165 |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Nickel |
| Net Weight | 0.118/g |
| Packaging Type | Reel |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.57mm max. |
| Wire Size AWG | 24, 26, 28, 30 |
| Wire Size mm² | N/A |

Solder Process Data


| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

| | |
|--------------------|--------------|
| Engineering Number | 7879-1(P154) |
|--------------------|--------------|

Reference - Drawing Numbers

| | |
|-------------------------|-----------------|
| Packaging Specification | PK-2759-002-001 |
| Sales Drawing | SD-7879 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[7879 Series](#)