USB 3.1 Type C Receptacle Mid-Mount DIP, 0.3mm Centre Height, Waterproof

multicomp PRO

RoHS

Compliant




Specifications USB Connector Type

opeeneenee	
USB Connector Type No. of Contacts	: USB 3.1 Type C Receptacle
	(IP-X7)
USB Connector Mounting	: Mid-Mount Through Hole
Contact Current Rating	: 5A (VBUS Pin, 1.5A/Pin)
0	5A (GND Pin, 1.25A/Pin Max)
	Other Pin: 0.25A/Pin
Insulation Resistance	: 100MΩ Min. @250VDC
Dielectric Withstanding Voltage	: 100VAC Min.
Low Level Contact Resistance	: Initial 40m Ω Max; After 50m Ω Max
Operating Temperature	: -40°C ~ 80°C
Mating Force	: 5 ~ 20N
Unmated Force	: 8 ~ 20N (Initial); 6 ~ 20N (After 10000 Cycles)
IP Rating	: IPX7

Material Specifications

Parameter	Material	Plating	Thickness
Housing	High Temp Plastic	Black	-
Terminal - A	Conner Niekol Silioon Alloy	Contact Area: 15µ" Gold Soldering Area: 1µ" Gold, 40µ" Nickel	T = 0.12mm
Terminal - B	Copper Nickel Silicon Alloy		T = 0.12mm
MID Plate	Stainless Steel	-	T = 0.15mm
GND Plate	Stainless Steel	Nickel Plating	T = 0.1mm
Shell - 1	Stainless Steel	Nickel Plating	T = 0.2mm
Shell - 2	Stainless Steel	Nickel Plating	T = 0.2mm
Glue Water	Ероху	Black	-

Diagram




Pin	Signal Name	Mating Sequence	Pin	Signal Name	Mating Sequence
A1	GND	First	B12	GND	First
A2	SSTXp1	Second	B11	SSRXp1	Second
A3	SSTXn1	Second	B10	SSRXn1	Second
A4	VBUS	First	B9	VBUS	First
A5	CC1	Second	B8	SBU2	Second
A6	Dp1	Second	B7	Dn2	Second
A7	Dn1	Second	<i>B6</i>	Dp2	Second
A8	SBU1	Second	B5	CC2	Second
A9	VBUS	First	B4	VBUS	First
A10	SSRXn2	Second	B3	SSTXn2	Second
A11	SSRXp2	Second	B2	SSTXp2	Second
A12	GND	First	B1	GND	First
SHEL	L	GND	SHEL	L	GND

Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



multicomp PRO



Part Number Table

	Description	Part Number
Dimensions : Millimetres	USB 3.1 Type C Receptacle, Waterproof, 24Pos, Mid-Mount DIP, 0.3mm Centre Height	MC002812

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

